

STUD BALL

MAGNETIC STUD FINDER

The Stud Ball is a protected magnetic stud finder that will out-perform all other types of magnetic stud finder on the market. Unlike other steel stud finders, the Stud Ball can detect metal through 1/2" or 5/8" drywall or other thicker building materials. Will also work through ceramic tiling and up to 3/4" plywood paneling.



- Rare Earth magnets with 27 lbs of pull
- No batteries required
- Detects screws or nails in wood frame walls



Part# 52300

PIPE SPINNER



Wrap a 10 foot pipe in 10 – 20 seconds! The Pipe Spinner allows you to speed up the process of taping IMC, galvanized conduit or black iron conduit in mil tape for underground applications. Instead of taping the pipe by hand, simply attach The Pipe Spinner to your drill and have your co-worker hold the tape while you spin the pipe.

- 1/4" drill attachment for quick change drills.
- Available in 2 sizes: 3/4 in. and 1 in.
- Saves time and money.

Part#
40907 - 3/4" thread
40910 - 1" thread



ROUGH-IN STICK

Part# 82000



Marks studs at 12", 18", 42", 48" & 60"

FEATURES:

- Easily mark stud walls for device installation
 - No need to use your tape measure while laying out devices
 - Telescopic pole aids in pulling wire above ceiling grids and areas of limited access
 - Extends up to 16'
- The Rough-In Stick allows you to mark out devices conveniently and efficiently by utilizing specifically designed holes to fit your felt marker. The Rod also features a telescopic pole for those tricky fishes.



THE FERRET

CABLE PULLING & FISHING TOOL

- Retains straightness when uncoiled, but will flex in the intended direction
- Non-conductive material with high tensile strength and outstanding durability
- Guide wheel designed to glide over obstructions and hard edges
- Ideal for wall cavities, suspended ceilings and confined space
- Includes a hook attachment for fishing cables

COMING SOON!

Part#
4 Meter - EP04M
8 Meter - EP08M





GPS LIGHTLOCK ASTRONOMICAL TIMERS

Onboard GPS does all your programming & maintenance

GPS LightLock automatically sets your date/ time & location, programs the switch times for your location, self-recovers from power outages & keeps the clock timed to the GPS atomic clock. You'll never have to deal with controls maintenance again, and you never pay a fee to use the GPS system!

Pays for itself many times over in servicing costs alone

Servicing controls is very expensive. Electricians perform hazardous work. They are well paid, as they should be. The retail price of GPS LightLock is a fraction of the cost of a single service trip charge to replace a photocell or re-program a timer. GPS LightLock now offers custom programming to meet your requirements stored in memory forever, and you still won't have to program a timer ever again. Still self-recovers from power outages and still requires no user programming, maintenance or even batteries!



Twist-Lock Astronomical
Timer 120-277VAC

Installs in under a minute!

The world's only fully automatic astronomical timer. Switches lights dusk-to-dawn anywhere in the world. Plug & play. Never needs programming. Self recovers from power outages. Direct replacement for twist-lock photocells.

Part# 85-GPS-MV-T



Wire-In Astronomical
Timer 120-277VAC

Our most popular model.

Includes twist-lock astronomical timer plus wire-in twist-lock socket with 1/2" standard female thread. Direct replacement for all wire-in photocells and programmable timers.

Part# 85-GPS-MV-W

THE WORLD'S MOST ACCURATE TIME KEEPING SYSTEM

GPS LightLock

- Self-Programming
- Maintenance Free for 15 Years
- Self-Recovers from Power Outages
- No Servers, Software or Network Infrastructure
- Nothing to Learn, Monitor or Maintain

TEMP-IT TEMPORARY LIGHT SOCKET

- Fits in most residential LED recessed cans
- Use A-19 Medium Base LED light bulb only
- Sold in boxes of 12 (lamps not included)




Part #99050


TRACER WIZARD TONER ADAPTOR

Features:

- Devices do not have to be taken offline to tone out
- Locating cables is fast and easy as long as the Wizard is connected between the tone generator & jack
- A must have tool for a toolbox
- No batteries required



TURN YOUR ANALOG TESTER INTO A DIGITAL ONE!



Part# 99060

PANEL BUDDY

KNOCKOUT SYSTEM

Tired of trying to remove knockouts? Let the Panel Buddy take care of them for you. This simple but genius tool removes knockouts in half the time, with half the effort.



Part# 7WBK100

- Kit removes knockouts on Electrical, Security, Alarm, and Datacom Panels.
- Works with lipped and non-lipped panels.



Tie Lips

Spend more time installing and less time picking up. The Tie Lips will hold your cable ties conveniently on your belt.

- Keeps your ties in place
- Quick and easy dispensing
- Holds different types and sizes
- Includes handy belt clip



Part# 43800

NUT BLASTER

UNIVERSAL WIRE CONNECTORS

- Fast, easy installation
- Prevents sore fingers and cramping hands
- Available in two sizes

The Nut Blaster makes quick work of tightening wire nuts. Simply attach the Nut Blaster to any standard drill and tighten your wire in seconds! Say goodbye to the carpal tunnel and hours wasted tightening wire nuts by hand. When the time comes to splice all your wires together you'll be able to finish each wire in 3-4 revolutions. The Nut Blaster will last you a lifetime with its high impact heat stabilized Delryn plastic construction and steel shaft. The Nut Blaster is compact and light making it the perfect addition to any electrician toolbag. Our XL edition is fitted for residential sized wires, and XXL for even larger jobs.



Part#
72101 - XL
(Fits all brands yellow, tan & red twist on wire connectors)
72102 - XXL
(Fits all brands large grey & blue twist on wire connectors)