

Project Name

Location

Prepared By



Notes

[www] 05-15-2023 01:50:04

General

Status	Active
Finish	White
Wattage	9W
Style	Utility
CCT (Kelvin)	2700K-5000K
Color Temperature	RGB & Tunable White
Length (in.)	14.00
Width (in.)	3.54
Height (in.)	1.00
Indoor or Outdoor Fixture	Indoor

Smart Product Info

IOT Enabled	Yes
Software Upgradeable	Yes
Communication Protocol	WiFi
Voice Assistants Supported	Siri Shortcuts; Alexa; Hey Google; SmartThings
Software Supported	Tuya/Starfish APP

Specifications

Technology	LED
CRI	90
Lumen Output	450L-538L
Rated Hours	25000
Voltage	120V
Dimmable	Yes-Dimmable
Dimming Note	Only with Starfish App
Beam Angle	110
Operating Temperature	-20C (-4F) to +45C (+113F)
Weight (lb.)	0.89
Sloped Ceiling	No
Fixture Material	Aluminum
Fixture Type	Under Cabinet
Max. Connectable Units	48

Compliance

Safety Listing	cETLus
Location Rating	Dry
Energy Star	Pending
CA T20 / T24 Rationale	California T24 2016 - 2022 JA8 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes
SDS Sheet	LED_Fixture

Additional Information

Warranty	5 Year Limited - Fixtures
----------	---------------------------



