



**SKU:** ACMN-2/0

**UPC:** 0783669021325

**Features & Benefits:**

**Description:** Aluminum Compression Pigtail Adaptor Conductor size 20, Tin Plated, cULus

## Specs

### Additional Class Attributes

Barrel Marking	Ink
Connecting Angle	180°
Connection	Compression
Contains DE-OX®	Yes
Flared End	No
ILSCOs Die Index Number	298
Number of Conductors	1
Replacement Part(s)	Cover

### Dimensions

Height BX (IN)	2.25
Weight BX (LB)	2.13
Width BX (IN)	5

### Material and Finish

Conductor Material	Copper/Aluminum
Connector Finish	Tin
Insulation	Supplied with insulating cover
Material	Aluminum

### Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

### General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 10
Dual Rated	Yes
NEMA Code	S-588-3
UPC Code	78366902132

### Testing Standards

**Prop65 Compliance**

WARNING: Cancer and Reproductive Harm -  
[www.P65warnings.ca.gov](http://www.P65warnings.ca.gov)

**UL Control Number**

941R

**UL / CULUS Specification**

UL/cUL 486A/B Listed

**UL File Number**

E62533

### *Environment and Temperature*

**Temperature Rating**

90°C

### *Color*

**Color**

Silver

**Color Code**

White

### *Voltage*

**Voltage Rating**

600 V

**Voltage Rating without cover**

35 kV

### *Conductor Ranges*

**Approximate Pin Size**

1 AWG