



**SKU:** ACMN-3/0

**UPC:** 0783669021349

**Features & Benefits:**

**Description:** Aluminum Compression Pigtail Adaptor Conductor size 30, Tin Plated, cULus

## Specs

### Additional Class Attributes

Barrel Marking	Ink
Connection	Compression
Contains DE-OX®	Yes
Flared End	No
ILSCOs Die Index Number	298
Number of Conductors	1
Replacement Part(s)	Cover

### Dimensions

Height BX (IN)	2.25
Weight BX (LB)	2.14
Width BX (IN)	5

### Material and Finish

Conductor Material	Copper/Aluminum
Connector Finish	Tin
Insulation	Supplied with insulating cover
Material	Aluminum

### Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

### General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 10
Dual Rated	Yes
NEMA Code	S-588-3
UPC Code	78366902134

### Testing Standards

Prop65 Compliance

WARNING: Cancer and Reproductive Harm -

[www.P65warnings.ca.gov](http://www.P65warnings.ca.gov)

UL Control Number

941R

UL / CULUS Specification

UL/cUL 486A/B Listed

UL File Number

E62525

### *Environment and Temperature*

Temperature Rating

90°C

### *Color*

Color

Silver

Color Code

White

### *Voltage*

Voltage Rating

600 V

Voltage Rating without cover

35 kV

### *Conductor Ranges*

Approximate Pin Size

10 AWG