



SKU: ACMN-350

UPC: 0783669021424

Features & Benefits:

Description: Aluminum Compression Pigtail Adaptor Conductor size 350, Tin Plated, cULus

Specs

Additional Class Attributes

| | |
|-------------------------|-------------|
| Barrel Marking | Ink |
| Connecting Angle | 180° |
| Connection | Compression |
| Contains DE-OX® | Yes |
| Flared End | No |
| ILSCOs Die Index Number | 299 |
| Number of Conductors | 1 |
| Replacement Part(s) | Cover |

Dimensions

| | |
|----------------|--------|
| Height BX (IN) | 2 |
| Weight BX (LB) | 1.72 |
| Width BX (IN) | 6.1875 |

Material and Finish

| | |
|--------------------|--------------------------------|
| Conductor Material | Copper/Aluminum |
| Connector Finish | Tin |
| Insulation | Supplied with insulating cover |
| Material | Aluminum |

Additional Technical Specifications

| | |
|----------------|----------|
| Conductor Type | Stranded |
|----------------|----------|

General

| | |
|-----------------------------|-----------------|
| Bag Quantity | 1 |
| Carton Quantity Description | STD PACK QTY 10 |
| Dual Rated | Yes |
| NEMA Code | S-588-3 |
| UPC Code | 78366902142 |

Testing Standards

Prop65 Compliance

WARNING: Cancer and Reproductive Harm -
www.P65warnings.ca.gov

UL Control Number

941R

UL / CULUS Specification

UL/cUL 486A/B Listed

UL File Number

E62545

Environment and Temperature

Temperature Rating

90°C

Color

Color

Silver

Color Code

Brown

Voltage

Voltage Rating

600 V

Voltage Rating without cover

35 kV

Conductor Ranges

Approximate Pin Size

250 kcmil