



SKU: ACMN-500

UPC: 0783669021455

Features & Benefits:

Description: Aluminum Compression Pigtail Adaptor Conductor size 500, Tin Plated, cULus

Specs

Additional Class Attributes

Barrel Marking	Ink
Connecting Angle	180°
Connection	Compression
Contains DE-OX®	Yes
Flared End	Yes
ILSCOs Die Index Number	300
Number of Conductors	1
Replacement Part(s)	Cover

Dimensions

Height BX (IN)	2.75
Weight BX (LB)	2.52
Width BX (IN)	6

Material and Finish

Conductor Material	Copper/Aluminum
Connector Finish	Tin
Insulation	Supplied with insulating cover
Material	Aluminum

Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 10
Dual Rated	No
NEMA Code	S-588-3
UPC Code	78366902145

Testing Standards

Prop65 Compliance

WARNING: Cancer and Reproductive Harm -
www.P65warnings.ca.gov

UL Control Number

941R

UL / CULUS Specification

UL/cUL 486A/B Listed

UL File Number

E62547

Environment and Temperature

Temperature Rating

90°C

Color

Color

Silver

Color Code

Pink

Voltage

Voltage Rating

600 V

Voltage Rating without cover

35 kV

Conductor Ranges

Approximate Pin Size

350 kcmil