



SKU: ACON-300

UPC: 0783669021417

Features & Benefits:

Description: Aluminum Compression Pigtail Adaptor offset, Conductor size 300, Tin Plated, cULus

Specs

Additional Class Attributes

Barrel Marking	Ink
Connecting Angle	180°
Connection	Compression
Contains DE-OX®	Yes
Flared End	No
ILSCOs Die Index Number	299
Number of Conductors	1
Replacement Part(s)	Cover

Dimensions

Height BX (IN)	2
Weight BX (LB)	1.98
Width BX (IN)	6.1875

Material and Finish

Conductor Material	Copper/Aluminum
Connector Finish	Tin
Insulation	Supplied with insulating cover
Material	Aluminum

Additional Technical Specifications

Conductor Type	Stranded
----------------	----------

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 10
Dual Rated	Yes
NEMA Code	S-588-3
UPC Code	78366902141

Testing Standards

Prop65 Compliance

WARNING: Cancer and Reproductive Harm -
www.P65warnings.ca.gov

UL Control Number

941R

UL / CULUS Specification

UL/cUL 486A/B Listed

UL File Number

E62543

Environment and Temperature

Temperature Rating

90°C

Color

Color

Silver

Color Code

Brown

Voltage

Voltage Rating

600 V

Voltage Rating without cover

35 kV

Conductor Ranges

Approximate Pin Size

4/0 AWG