



Safety Data Sheet

Copyright, 2014, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document Group:	07-3297-4	Version Number:	7.00
Issue Date:	10/08/14	Supersedes Date:	12/06/13

SECTION 1: Identification

1.1. Product identifier

Wire Pulling Lubricant Wintergrade WLW Series (WLW-QT, WLW-1, WLW-5)

Product Identification Numbers

80-6108-3368-5, 80-6108-3369-3, 80-6108-3370-1, 80-6108-3371-9

1.2. Recommended use and restrictions on use

Recommended use

WIRE PULLING LUBRICANT, WIRE PULLING LUBRICANT

1.3. Supplier's details

MANUFACTURER:	3M
DIVISION:	Electrical Markets Division
ADDRESS:	3M Center, St. Paul, MN 55144-1000, USA
Telephone:	1-888-3M HELPS (1-888-364-3577)

1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

SECTION 2: Hazard identification

2.1. Hazard classification

Not classified as hazardous according to OSHA Hazard Communication Standard, 29 CFR 1910.1200.

2.2. Label elements

Signal word

Not applicable.

Symbols

Not applicable.

Pictograms

Not applicable.

2.3. Hazards not otherwise classified

None.

SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
WATER	7732-18-5	75 - 80
PROPYLENE GLYCOL	57-55-6	15 - 19 Trade Secret *
POLYETHYLENE GLYCOL	25322-68-3	0.1 - 2
GLYCOLS, POLYPROPYLENE	25322-69-4	0.1 - 2
SODIUM POLYACRYLATE	9003-04-7	0.1 1

*The specific chemical identity and/or exact percentage (concentration) of this composition has been withheld as a trade secret.

SECTION 4: First aid measures**4.1. Description of first aid measures****Inhalation:**

No need for first aid is anticipated.

Skin Contact:

Wash with soap and water. If signs/symptoms develop, get medical attention.

Eye Contact:

Flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms persist, get medical attention.

If Swallowed:

Rinse mouth. If you feel unwell, get medical attention.

4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1. Information on toxicological effects.

4.3. Indication of any immediate medical attention and special treatment required

Not applicable.

SECTION 5: Fire-fighting measures**5.1. Suitable extinguishing media**

Material will not burn. Use a fire fighting agent suitable for the surrounding fire.

5.2. Special hazards arising from the substance or mixture

None inherent in this product.

Hazardous Decomposition or By-Products**Substance**

Carbon monoxide
Carbon dioxide

Condition

During Combustion
During Combustion

5.3. Special protective actions for fire-fighters

No special protective actions for fire-fighters are anticipated.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Ventilate the area with fresh air. Observe precautions from other sections.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Working from around the edges of the spill inward, cover with bentonite, vermiculite, or commercially available inorganic absorbent material. Mix in sufficient absorbent until it appears dry. Remember, adding an absorbent material does not remove a physical, health, or environmental hazard. Collect as much of the spilled material as possible. Place in a closed container approved for transportation by appropriate authorities. Clean up residue with water. Seal the container. Dispose of collected material as soon as possible.

SECTION 7: Handling and storage**7.1. Precautions for safe handling**

For industrial or professional use only. Do not eat, drink or smoke when using this product. Wash thoroughly after handling.

7.2. Conditions for safe storage including any incompatibilities

No special storage requirements.

SECTION 8: Exposure controls/personal protection**8.1. Control parameters****Occupational exposure limits**

If a component is disclosed in section 3 but does not appear in the table below, an occupational exposure limit is not available for the component.

Ingredient	C.A.S. No.	Agency	Limit type	Additional Comments
POLYETHYLENE GLYCOL	25322-68-3	AIHA	TWA(as particulate):10 mg/m3	
GLYCOLS, POLYPROPYLENE	25322-69-4	AIHA	TWA(as aerosol):10 mg/m3	
PROPYLENE GLYCOL	57-55-6	AIHA	TWA(as aerosol):10 mg/m3	

ACGIH : American Conference of Governmental Industrial Hygienists

AIHA : American Industrial Hygiene Association

CMRG : Chemical Manufacturer's Recommended Guidelines

OSHA : United States Department of Labor - Occupational Safety and Health Administration

TWA: Time-Weighted-Average

STEL: Short Term Exposure Limit

CEIL: Ceiling

8.2. Exposure controls**8.2.1. Engineering controls**

Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapors/spray. If ventilation is not adequate, use respiratory protection equipment.

8.2.2. Personal protective equipment (PPE)**Eye/face protection**

Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:

Safety Glasses with side shields

Skin/hand protection

No protective gloves required.

Respiratory protection

An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for particulates

For questions about suitability for a specific application, consult with your respirator manufacturer.

SECTION 9: Physical and chemical properties**9.1. Information on basic physical and chemical properties**

General Physical Form:	Liquid
Specific Physical Form:	Gel
Odor, Color, Grade:	OPAQUE, LIGHT-GREEN VISCOUS GEL WITH NO ODOR
Odor threshold	<i>No Data Available</i>
pH	6.5 - 8.5
Melting point	10 °F
Boiling Point	>=212 °F
Flash Point	No flash point
Evaporation rate	Approximately 1 Units not avail. or not appl. [<i>Ref Std:</i> WATER=1]
Flammability (solid, gas)	Not Applicable
Flammable Limits(LEL)	<i>No Data Available</i>
Flammable Limits(UEL)	<i>No Data Available</i>
Vapor Pressure	Approximately 18 mmHg [<i>Details:</i> @20C.]
Vapor Density	0.9 - 1.1 [<i>Ref Std:</i> AIR=1]
Density	<i>Not Applicable</i>
Specific Gravity	Approximately 1.01 Units not avail. or not appl. [<i>Ref Std:</i> WATER=1]
Solubility in Water	Complete
Solubility- non-water	<i>No Data Available</i>
Partition coefficient: n-octanol/ water	<i>Not Applicable</i>
Autoignition temperature	<i>Not Applicable</i>
Decomposition temperature	<i>No Data Available</i>
Viscosity	70,000 - 110,000 centipoise [<i>Test Method:</i> Brookfield]
Average particle size	<i>Not Applicable</i>
Bulk density	<i>Not Applicable</i>
Hazardous Air Pollutants	<i>Not Applicable</i>
Molecular weight	<i>Not Applicable</i>
Volatile Organic Compounds	18 %
Percent volatile	97 % weight
Softening point	<i>Not Applicable</i>
VOC Less H2O & Exempt Solvents	18 %

SECTION 10: Stability and reactivity**10.1. Reactivity**

This material is considered to be non reactive under normal use conditions.

10.2. Chemical stability

Stable.

10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

10.4. Conditions to avoid

None known.

10.5. Incompatible materials

None known.

Not Applicable

10.6. Hazardous decomposition products

Substance

Aldehydes

Condition

Oxidation, heat or reaction

Refer to section 5.2 for hazardous decomposition products during combustion.

SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

11.1. Information on Toxicological effects

Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation:

No health effects are expected.

Skin Contact:

Contact with the skin during product use is not expected to result in significant irritation.

Eye Contact:

Contact with the eyes during product use is not expected to result in significant irritation.

Ingestion:

Gastrointestinal Irritation: Signs/symptoms may include abdominal pain, stomach upset, nausea, vomiting and diarrhea.

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

Name	Route	Species	Value
------	-------	---------	-------

Overall product	Ingestion		No data available; calculated ATE > 5,000 mg/kg
PROPYLENE GLYCOL	Dermal	Rabbit	LD50 20,800 mg/kg
PROPYLENE GLYCOL	Ingestion	Rat	LD50 22,000 mg/kg
GLYCOLS, POLYPROPYLENE	Dermal	Rabbit	LD50 > 10,000 mg/kg
POLYETHYLENE GLYCOL	Dermal	Rabbit	LD50 > 20,000 mg/kg
GLYCOLS, POLYPROPYLENE	Ingestion	Rat	LD50 > 2,000 mg/kg
POLYETHYLENE GLYCOL	Ingestion	Rat	LD50 32,770 mg/kg
SODIUM POLYACRYLATE	Dermal	Rabbit	LD50 > 5,000 mg/kg
SODIUM POLYACRYLATE	Ingestion	Rat	LD50 > 2,000 mg/kg

ATE = acute toxicity estimate

Skin Corrosion/Irritation

Name	Species	Value
PROPYLENE GLYCOL	Rabbit	No significant irritation
GLYCOLS, POLYPROPYLENE	Rabbit	No significant irritation
POLYETHYLENE GLYCOL	Rabbit	Minimal irritation
SODIUM POLYACRYLATE	Rabbit	No significant irritation

Serious Eye Damage/Irritation

Name	Species	Value
PROPYLENE GLYCOL	Rabbit	No significant irritation
GLYCOLS, POLYPROPYLENE	Rabbit	No significant irritation
POLYETHYLENE GLYCOL	Rabbit	Mild irritant
SODIUM POLYACRYLATE	Rabbit	No significant irritation

Skin Sensitization

Name	Species	Value
PROPYLENE GLYCOL	Human	Some positive data exist, but the data are not sufficient for classification
POLYETHYLENE GLYCOL	Guinea pig	Not sensitizing

Respiratory Sensitization

Name	Species	Value
------	---------	-------

Germ Cell Mutagenicity

Name	Route	Value
PROPYLENE GLYCOL	In Vitro	Not mutagenic
PROPYLENE GLYCOL	In vivo	Not mutagenic
POLYETHYLENE GLYCOL	In Vitro	Not mutagenic
POLYETHYLENE GLYCOL	In vivo	Not mutagenic

Carcinogenicity

Name	Route	Species	Value
PROPYLENE GLYCOL	Dermal	Mouse	Not carcinogenic
PROPYLENE GLYCOL	Ingestion	Multiple animal species	Not carcinogenic
POLYETHYLENE GLYCOL	Ingestion	Rat	Not carcinogenic

Reproductive Toxicity

Reproductive and/or Developmental Effects

Name	Route	Value	Species	Test Result	Exposure Duration
PROPYLENE GLYCOL	Ingestion	Not toxic to female reproduction	Mouse	NOAEL 10,100 mg/kg/day	2 generation
PROPYLENE GLYCOL	Ingestion	Not toxic to male reproduction	Mouse	NOAEL 10,100 mg/kg/day	2 generation
PROPYLENE GLYCOL	Ingestion	Not toxic to development	Multiple animal	NOAEL 1,230	during organogenesis

			species	mg/kg/day	s
POLYETHYLENE GLYCOL	Ingestion	Not toxic to female reproduction	Rat	NOAEL 1,125 mg/kg/day	during gestation
POLYETHYLENE GLYCOL	Ingestion	Not toxic to male reproduction	Rat	NOAEL 5699 +/- 1341 mg/kg/day	5 days
POLYETHYLENE GLYCOL	Not Specified	Some positive reproductive/developmental data exist, but the data are not sufficient for classification		NOEL N/A	
POLYETHYLENE GLYCOL	Ingestion	Some positive developmental data exist, but the data are not sufficient for classification	Mouse	NOAEL 562 mg/animal/day	during gestation

Target Organ(s)**Specific Target Organ Toxicity - single exposure**

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
PROPYLENE GLYCOL	Ingestion	central nervous system depression	May cause drowsiness or dizziness	Human	NOAEL Not available	poisoning and/or abuse
POLYETHYLENE GLYCOL	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 1.008 mg/l	2 weeks

Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
PROPYLENE GLYCOL	Ingestion	hematopoietic system	Some positive data exist, but the data are not sufficient for classification	Multiple animal species	NOAEL 1,370 mg/kg/day	117 days
PROPYLENE GLYCOL	Ingestion	kidney and/or bladder	All data are negative	Dog	NOAEL 5,000 mg/kg/day	104 weeks
POLYETHYLENE GLYCOL	Inhalation	respiratory system	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 1.008 mg/l	2 weeks
POLYETHYLENE GLYCOL	Ingestion	kidney and/or bladder	Some positive data exist, but the data are not sufficient for classification	Rat	NOAEL 5,640 mg/kg/day	13 weeks
POLYETHYLENE GLYCOL	Ingestion	heart endocrine system hematopoietic system liver nervous system	All data are negative	Rat	NOAEL 5,640 mg/kg/day	13 weeks

Aspiration Hazard

Name	Value

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

SECTION 12: Ecological information**Ecotoxicological information**

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

SECTION 13: Disposal considerations

13.1. Disposal methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Prior to disposal, consult all applicable authorities and regulations to insure proper classification. Dispose of waste product in a permitted industrial waste facility. Empty and clean product containers may be disposed as non-hazardous waste. Consult your specific regulations and service providers to determine available options and requirements.

EPA Hazardous Waste Number (RCRA): Not regulated

SECTION 14: Transport Information

For Transport Information, please visit <http://3M.com/Transportinfo> or call 1-800-364-3577 or 651-737-6501.

SECTION 15: Regulatory information

15.1. US Federal Regulations

Contact 3M for more information.

311/312 Hazard Categories:

Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - Yes Delayed Hazard - No

15.2. State Regulations

Contact 3M for more information.

15.3. Chemical Inventories

The components of this material are in compliance with the provisions of Australia National Industrial Chemical Notification and Assessment Scheme (NICNAS). Certain restrictions may apply. Contact the selling division for additional information.

The components of this product are in compliance with the new substance notification requirements of CEPA.

The components of this material are in compliance with the China "Measures on Environmental Management of New Chemical Substance". Certain restrictions may apply. Contact the selling division for additional information.

The components of this material are in compliance with the provisions of the Korean Toxic Chemical Control Law. Certain restrictions may apply. Contact the selling division for additional information.

The components of this material are in compliance with the provisions of Japan Chemical Substance Control Law. Certain restrictions may apply. Contact the selling division for additional information.

The components of this material are in compliance with the provisions of Philippines RA 6969 requirements. Certain restrictions may apply. Contact the selling division for additional information.

The components of this product are in compliance with the chemical notification requirements of TSCA.

Contact 3M for more information.

15.4. International Regulations

Contact 3M for more information.

This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: Other information

NFPA Hazard Classification

Health: 0 Flammability: 0 Instability: 0 Special Hazards: None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

Document Group:	07-3297-4	Version Number:	7.00
Issue Date:	10/08/14	Supersedes Date:	12/06/13

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M

3M USA SDSs are available at www.3M.com