

Project Name

Location

Prepared By



SATCO S11840

9WLED/GBL/4/CCT/RND/WH

Notes

[www] 05-15-2023 01:50:09

General

Status	Active
Recessed Can Size	4 in.
Wattage	9W
Voltage	120V
Finish	White
CCT (Kelvin)	2700K/3000K/3500K/4000K/5000K
Color Temperature	Warm to Cool White
Lumen Output	650L-750L
Indoor or Outdoor Fixture	Indoor

Specifications

Technology	LED
CRI	90
Beam Angle	36
Rated Hours	50000
Operating Temperature	-20C (-4F) to +45C (+113F)
Dimmable	Yes-Dimmable
Sloped Ceiling	Yes

Dimensions

Width (in.)	4.92
Height (in.)	1.42
Weight (lb.)	1.00

Compliance

Safety Listing	cETLus - Listed
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2393126
Air Tight Rated	Yes
IC Rated	Yes
CA T20 / T24 Rationale	California T24 2016 - 2022 JA8 Listed
California Status	Lawful for sale in California
Title 20 / 24 Status	California T24 Listed
California Prop 65	Lead
RoHS Compliant	Yes
FCC Compliant	Yes

Additional Information

Additional Information	Candlepower: 750
Warranty	5 Year Limited - Fixtures