



Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V AFCI Circuit Breakers - 1-Pole, AFCI Combo - BAF, 10KAIC, 120VAC are Circuit Protection Molded Case Circuit Breakers. Sub Brand: N/A Type: BL Special Features: N/A Application: Electrical Distribution Standard: UL 1699 Voltage Rating: 120V Amperage Rating: 20A Load Rating: N/A Frequency Rating: N/A Phase: N/A Frame: N/A Trip Type: N/A Trip Range: Thermal Magnetic Interrupt Rating: 10 AIC Number Of Poles: 1P

General technical data	
number of poles	1
suitability for operation	Electrical Distribution
Electricity	
continuous current rated value	20 A
Model	
product brand name	SIEMENS
type of electrical connection	BOLT-ON
Mechanical Design	
depth [in]	1 in
design of the product	BL
height [in]	5.3 in
width [in]	3 in
General product approval	
standard	UL 1699

last modified: 3/17/2023 

