



# Switch Start Metal Halide Standard

## MH175/C/U 12PK

High performance, Long life and Superior light quality. A compact, energy efficient metal halide lamp that provides crisp, sparkling light with long life and high efficiency.

### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

### Product data

<b>Operating and Electrical</b>		<b>Color rendering index (CRI)</b>	
Power Consumption	175 W	>60	
Wattage Equivalent	175 W	<b>Controls and Dimming</b>	
Warm-up time to 60% light	<120 s	Dimmable	
<b>General Information</b>		No	
Cap-Base	E39 [Single Contact Mogul Screw]	<b>Mechanical and Housing</b>	
<b>Light Technical</b>		Bulb Finish	
Luminous Flux	8,645 lumen	Coated glass	
Chromaticity Coordinate X (Nom)	0.385	Bulb Material	
Chromaticity Coordinate Y (Nom)	0.39	Hard Glass	
Correlated Color Temperature (Nom)	3900 K	Bulb Shape	
Luminous Efficacy (Rated) (Min)	64 lm/W	BD17	
Luminous Efficacy (rated) (Nom)	76 lm/W	<b>Approval and Application</b>	
		Mercury (Hg) Content (Max)	
		30 mg	
		<b>Product Data</b>	
		Order product name	
		MH175/C/U 12PK	

Switch Start Metal Halide Standard

Order code	928601150403
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	12
Material number (12NC)	928601150403

Full product name	MH175/C/U 12PK
EAN/UPC - Case	50046677287288

Dimensional drawing

Product	D (max)	C (max)
MH175/C/U 12PK	90 mm	206 mm

