



# Pulse Start Metal Halide Standard

## MS750/BU/PS 6PK

Philips Pulse Start Metal Halide Lamps offer an optimized metal halide system for greater efficiency and lumen maintenance.

### Warnings and Safety

- R "WARNING: These lamps can cause serious skin burn and eye inflammation from short wave ultraviolet radiation if outer envelope of the lamp is broken or punctured. Do not use where people will remain for more than a few minutes unless adequate shielding or other safety precautions are used. Certain lamps that will automatically extinguish when the outer envelope is broken or punctured are commercially available." This lamp complies with FDA radiation performance standard 21 CFR subchapter J. (USA:21 CFR 1040.30 Canada: SOR/DORS/80-381)

### Product data


General Information	
Cap-Base	E39 [Single Contact Mogul Screw]
Light Technical	
Luminous Flux	53,300 lumen
Color Designation	4000 Kelvin
Chromaticity Coordinate X (Nom)	0.385
Chromaticity Coordinate Y (Nom)	0.4
Correlated Color Temperature (Nom)	4000 K
Luminous Efficacy (Rated) (Min)	98 lm/W
Luminous Efficacy (rated) (Nom)	109 lm/W
Color rendering index (CRI)	>65
Warm-up time to 60% light	<180 s
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Bulb Material	Hard Glass
Bulb Shape	BT37
Approval and Application	
Mercury (Hg) Content (Max)	125 mg
Product Data	
Order product name	MS750/BU/PS 6PK
Order code	928601179101

## Pulse Start Metal Halide Standard

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	6
Material number (12NC)	928601179101
Full product name	MS750/BU/PS 6PK

EAN/UPC - Case	50046677135404
----------------	----------------

### Dimensional drawing



Product	D (max)	C (max)
MS750/BU/PS 6PK	122 mm	282 mm

