



Non-Metallic Vapour Barrier Ceiling Box

By Raco
Catalog # 2028FBAR



Non-metallic box, 4 In. Round Ceiling Box, For use with non-metallic sheathed cable, Flanged with Vapour Barrier, 28.1 Cu. In., Round box with flush bracket, 1/2 in. setback, Cable clamps (40-Pack)

Features

- Self-clamping wire entry clamps
- Vapour/air barrier flange and integral wire entry seal provides superior energy savings and quick installation
- Hands free installation for 1/2", 5/8", or 3/4" drywall
- Front mounted grounding screw with combination straight/Robertson head

General

Bracket Setback	0.50
Cable Clamps	4
Color	<ul style="list-style-type: none">• Yellow• Jaune
Material	Thermoplastic Resin
Style	Vapor Barrier
Type	<ul style="list-style-type: none">• Vapor Barrier Box• Box
UPC	805035054536
Wiring System	Nonmetallic Sheathed Cable

Dimensions

Dimensions	6.93 in x 5.118 in x 3.150 in
Fixture Lbs.	50 lb
Height	3.150 in
Length	6.93 in
Weight	.265 lb
Width	5.118 in

Certifications and Compliance

Certified Listed	CSA
------------------	-----

Logistics

Carton Quantity	40
Pallet Quantity	1600

Product Assets

- [3D Product View](#)
- [Brochures - H3672 Banana Boxes](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
RACO_2028FBAR_SPEC | REV 3/2023