



PROclick Connector, LC, OM3/OM4, Aqua, 100 Pack

By Hubbell Premise Wiring
Catalog Number [FCLC900K50GM100](#)



Fiber Optic Connectors, ProClick LC, OM3/OM4, Pre-Polished,
10GHz 900, 12Pack.

Features

- Terminate in Less than 60 Seconds
- RoHS Compliant and Bulk Packed in Recyclable Cartons

Application

Interconnect

General

Color	Aqua
Connector Type	LC
Performance	<ul style="list-style-type: none">• Optical - Insertion loss - 0.5dB (0.35dB typical), 0.75dB max• Optical - Mating durability - 500 cycles <• 0.1dB change• Optical - Multimode return loss - 35dB Typ, 22dB minimum• Optical - Singlemode return loss - 55dB Typ, 40dB minimum• Environmental - Operating temperature - 0 °C to +70 °C
Style	PROclick
Sub Brand	OptiChannel
UPC	662620237435

Electrical Ratings

Connectivity Fiber Optic Connector

Conductor Related

Fiber Type OM3/OM4, MM

Certifications and Compliance

Industry Standard(s)

- Telcordia GR-326-CORE
- TIA-568-C.3
- TIA-604-FOCIS

Logistics

Carton Quantity 100

Product Assets

[Catalog Page - Premise Catalog Page A-8](#)
[Catalog Page - Premise Catalog Page G-3](#)
[Video - ProClick Fiber Optic Connector Installation](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
PREM_CA-FCLC900K50GM100-SPEC-EN | REV 5/2023