




# Compression Splice

By Burndy  
Catalog # YSP34T



500 kcmil CU, Tapered End, Internal Chamfer, Tin Plated, UL/CSA, 90°C, Up to 35kV, BROWN Color Code, 20 or 299 Die Index.

## Application

Wire Splice

## General

Color Code	Brown
Connector Type	LONG BARREL
Die Index	20
EU RoHS Indicator	Yes
Feature - Barrel Style	Tapered
Feature - Barrel Type	Standard
Finish Type	Tin-Plated
Material	COPPER
Plated	Y
Plating Type	Electro Tin plated
Sub Brand	HYLINK
Trade Name	HYLINK™
Type	YSP-T, High Voltage, Long Barrel
UPC	781810001332

## Dimensions

Dimension - B Length inch	1.71 in
Dimension - L Length Overall mm	90 mm
Dimension - Length Overall inch	3.55 in
Dimension - Strip Length inch	1-3/4 in

## Electrical Ratings

Voltage Rating	35 kV
----------------	-------

## Conductor Related

Conductor - Copper Str Size	500 kcmil
Conductor - Copper Str Size Range	500 kcmil
Conductor - Material	COPPER
Conductor Size	500 KCMIL
Conductor Type	CODE
Wire Size	500 kcmil

## Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	25
Minimum Pack Quantity	1
Pallet Quantity	5550

## Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - sc20445-01](#)



A proud member of the Hubbell Family.