



## BF18 Flexible Copper Braid

By Burndy  
Catalog # [BF18](#)

Flexible Cu Braid Jumper, 18" L, Amp Rating: 360(Indoor), 430(Outdoor)



### Application

For Use On: Designed to take up linear expansion and contraction, compensate for misalignment and absorb vibratory movement of electrical equipment and devices

### General

Connector Type	Braid
Construction Material - Main	Copper
EU RoHS Indicator	Yes
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Sub Brand	BRAID JUMPER
Type	B, Flexible
UPC	781810005125
UPC 12 Digit	7818100051255

### Dimensions

Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.44 in
Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18.00 in
Dimension - N inch	0.75 in
Dimension - Pad Width inch	1.19 in
Length	18 in

### Electrical Ratings

Rating - Indoor Amperage	360 A
Rating - Outdoor Amperage	430 A

### Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SE..210201-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-BF18-SPEC-EN | REV 8/2023