



## BG24N Flexible Copper Braid, 24 in L, .25 IN Thickness

By Burndy  
Catalog # [BG24N](#)

Flexible Copper Braid, 24 in L, .25 IN Thickness.



### Application

Flexible copper braid jumpers designed to take up linear expansion and contraction

### General

Connector Type	Braid
EU RoHS Indicator	Yes
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	N
Sub Brand	BRAID
Type	B, Flexible
UPC	781810005262
UPC 12 Digit	7818100052622

### Dimensions

Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	610 mm
Dimension - Length Overall inch	24.00 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.50 in
Length	24 in

### Electrical Ratings

Rating - Indoor Amperage	415
Rating - Outdoor Amperage	495

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

### Logistics

Minimum Pack Quantity	1
-----------------------	---

### Product Assets

[Catalogs - Full Line BURNDY Catalog](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SE..210201-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.  
BRDY-BG24N-SPEC-EN | REV 8/2023