



BE18N Flexible Copper Braid, 18 in L, Approximate ampere rating indoor:340, outdoor:405

By Burndy
Catalog # [BE18N](#)

Flexible Copper Braid, 18 in L, Approximate ampere rating indoor:340, outdoor:405.



Application

Flexible copper braid jumpers designed to take up linear expansion and contraction

General

Connector Type	Braid
EU RoHS Indicator	Yes
Material	Copper
Material - Ferrules	Y
Physical Attribute - Number of Braids	1
Plated	Y
Sub Brand	BRAID
Type	B, Flexible
UPC	781810005330
UPC 12 Digit	7818100053300

Dimensions

Dimension - D inch	3.00 in
Dimension - Hole Size inch	0.56 in
Dimension - L Length Overall mm	457 mm
Dimension - Length Overall inch	18.00 in
Dimension - N inch	0.62 in
Dimension - Pad Width inch	1.50 in
Length	18 in

Electrical Ratings

Rating - Indoor Amperage	340
Rating - Outdoor Amperage	405

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

Product Assets

[Customer Notices - Prop 65 Notice](#)
[Sales Drawings - 10036839](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-BE18N-SPEC-EN | REV 8/2023