

# KLU70, Mechanical Offset Tongue, #8 Sol-#2 AWG Str, 1-Hole, 1/4" Stud, 1 Screw

By Burndy Catalog # KLU70

Copper Terminal, Offset Tongue, 1 Hole, 8 AWG (Sol)-2 AWG (Str), 1/4" Stud, 1 Screw.



# **Application**

For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bar

## General

Connector Type Pressure Bar

**EU RoHS Indicator** 

5/16 UNF Slotted SetScrew Hardware Type

Installation Torque 40

Recommended in-lb

Material Copper

Physical Attribute - Number of 1

Holes

Physical Attribute - Number of 1

Screws

Physical Attribute - Screw Slot

Type

Plated N Plating Type Unplated Sub Brand **SCRULUG** 

Trade Name SCRULUG™

Type **Bolted Lugs & Terminals** 

UPC 781810351383

### **Dimensions**

Dimension - B Length fraction 1/2 in Dimension - B Length inch 0.50 in Dimension - Bolt Size fraction 1/4 Dimension - Hole Size inch 0.26 in Dimension - Hole Size mm 7 mm Dimension - L Length Overall 39 mm

mm

Dimension - Length Overall

inch

Dimension - N inch 0.25 in Dimension - Pad Width inch 0.47 in Dimension - Screw Size inch 5/16 Dimension - Strip Length inch 3/4 Dimension - Stud Size inch

#### **Conductor Related**

Conductor - Copper Solid Size 8 AWG;7 AWG;6 AWG;5

AWG;4 AWG;3 AWG;2 AWG

Conductor - Copper Solid Size 8 AWG-2 AWG

Conductor - Copper Str Size 8 AWG;7 AWG;6 AWG;5

AWG;4 AWG;3 AWG;2 AWG

Conductor - Copper Str Size

Range

Conductor Size 8-2 AWG

• CU C Solid-Size Conductor Type

• CU C Str-Size

8 AWG-2 AWG

# **Certifications and Compliance**

Certification - CSA Approved Certification - ETL No Certification - UL Listed Direct No

Burial

Certification - UL Recognized Nο Certification - cULus Industry Standard(s) **UL467** Standards - Industry **UL467** 

Standards Met

Standards - RoHS Compliance

Status

**UL** Listed No

# Logistics

Carton Quantity 600 Minimum Pack Quantity 1

# **Product Assets**

Catalogs - Full Line BURNDY Catalog Customer Notices - Prop 65 Notice Sales Drawings - sd207469-01



1.55 in