



BF12 Flexible Copper Braid

By Burndy
Catalog # [BF12](#)

Copper Braid, 12" Long, 1 Braid, 2 Holes 2 Ferrules, 7/16" Stud, 1-1/2" Stud Hole Spacing, 360 amps Indoor, 430 amps Outdoor.



General

| | |
|---------------------------------------|----------------------|
| Connector Type | Braid |
| Construction Material - Main | Copper |
| EU RoHS Indicator | Contact Manufacturer |
| Material | Copper |
| Material - Ferrules | Y |
| Physical Attribute - Number of Braids | 1 |
| Plated | Y |
| Sub Brand | Braid |
| Type | B |
| UPC | 781810807040 |
| UPC 12 Digit | 7818108070400 |

Dimensions

| | |
|---------------------------------|----------|
| Dimension - D inch | 3.00 in |
| Dimension - Hole Size inch | 0.44 in |
| Dimension - L Length Overall mm | 305 mm |
| Dimension - Length Overall inch | 12.00 in |
| Dimension - N inch | 0.75 in |
| Dimension - Pad Width inch | 1.19 in |
| Length | 12 in |

Electrical Ratings

| | |
|---------------------------|-----|
| Rating - Indoor Amperage | 360 |
| Rating - Outdoor Amperage | 430 |

Certifications and Compliance

| | |
|---|-------|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Listed Direct Burial | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL467 |
| Standards - Industry Standards Met | UL467 |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

Product Assets

[Catalogs - Full Line BURNDY Catalog](#)
[Sales Drawings - SE..210201-01](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-BF12-SPEC-EN | REV 8/2023