




radiant Collection  
radiant® LED/CFL Dimmer, Two Wire, Tri-Color  
Part No. RHL373PTC



Upgrade your space with precise dimming control and exceptional style. This dimmer from the radiant® Collection is optimized for use with LED 2-wire bulbs and fixtures compliant with the SSL 7A standard for energy efficiency. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Designed to save energy, this dimmer is for use with LED bulbs and fixtures also designed to the SSL 7A standard for efficiency. For use in both single-pole and 3-way applications.

Low-profile paddle switch offers smoother On/Off control, while a separate, ergonomic slider allows you to adjust light levels with precision.

Locator light illuminates when switch is off, emitting a soft glow to help you find it in the dark.

Constant memory features returns lights to their previous level after a power failure or outage.

No derating\* required for 2-gang applications. \*Reducing the maximum wattage a dimmer can handle. This is sometimes required for multi-gang applications.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White, Ivory, Light Almond
Finish	Matte	UPC Number	785007161922
Country Of Origin	China	Features	Locator Light
Switch Type	Paddle, Slider	Number of Switches	1
Application Sector	Residential	Warranty Type	Limited Lifetime Warranty
Type	Dimmer		

---

## Dimensions

---

Product Width US 1.29 in

Product Depth US 1.0 in

---

Product Height US 3.18 in

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed Yes

---

## Technical Information

---

Number of Gangs 1

Amperage 2.1 A

---

Bulb Compatibility LED, CFL, Incandescent, Halogen

Number of Poles Single Pole, 3-Way

---

Wattage 300 W

Mounting Type Box

---

Voltage 0 V, 120 V

---