

# Lumaris Tunable White Tape Light

The Lumaris tunable white tape light takes scene control to the next level, offering a simple and seamless way to add tunable white accent lighting to Lutron connected home projects.

Built on the ultra-reliable Lutron Clear Connect-Type X wireless technology, the Lumaris tunable white tape light is a native component within the Lutron platform including controls, apps, programming software, and the Lutron Connect cloud services.

A complete Lumaris tunable white tape light solution consists of field-cut tunable white tape, a wireless controller with integrated LED drivers, high-reliability punch connectors, dedicated wiring, and a plug-in power supply. LED tape aluminum mounting channel and lens sold separately by others.


#### **Features**

#### **Lighting System**


- Seamless integration with HomeWorks QSX and Radio RA3
- User programmable intensity and color temperature presets
- Warm dim to mimic the dimming curve of an incandescent lamp
- Automatically changes color temperature based on time of day
- Manual adjustments via the app or integration

## Wireless Controller (with plug-in power supply)

- Continuous, flicker-free dimming from 100% down to 0.1% of measured light output<sup>1</sup>
- 32 W rated load (16.4 ft [5 m] of LED tape)
- 50,000 hours rated lifetime<sup>2</sup>
- Ambient operating temperature: 32°F to 104°F (0°C to 40°C)
- Uses Clear Connect-Type X wireless communication
- Output short-circuit and overload-protection
- Low profile, easy to hide
- Barrel jack connection for easy installation







**Power Supply** 

**LED Tape** 

#### **LED Tape**

- 2-channel tunable white
- Two tape ranges available:
  - Soft White Tape: 1800K 3000K
  - Daylight Tape: 2500K 5000K
- 90+ CRI (color rendering index)
- 3 step MacAdam ellipse (SDCM)
- Lumen output: 200 lumens per foot typical
- Luminous efficacy: 100 lumens per Watt typical
- Power consumption: 1.8 Watts per foot typical
- Rated life: L70 50,000 hours
- 2 in (50.8 mm) cuttable segments
- Strong VHB adhesive
- Indoor damp/dry location rated
- Wardrobe closet rated

<sup>&</sup>lt;sup>1</sup> Tunable white performance is maintained from 100% to 1%.

Plug-in power supply lifetime is rated for 50,000 hours in up to a 77 °F (25 °C) ambient temperature. Increasing ambient temperature may degrade lifetime.



# Lumaris Tunable White Tape Light

#### **Model Numbers**

Model Number				
HomeWorks QSX	RadioRA 3	Description		
HWL-TLK-SW	RRL-TLK-SW	Soft White Kit  Wireless controller (with plug-in power supply)  Soft white LED tape (1800 K - 3000 K) - 16.4 ft (5 m) reel  Wire/tape connectors (5 pack)  3 conductor cable - 10 ft (3 m)		
HWL-TLK-DL	RRL-TLK-DL	Daylight Kit  Wireless controller (with plug-in power supply)  Daylight LED tape (2500 K - 5000 K) - 16.4 ft (5 m) reel  Wire/tape connectors (5 pack)  3 conductor cable - 10 ft (3 m)		
HWL-TWC-WH	RRL-TWC-WH	Wireless controller (including power supply)		
LU-TO5-SW		Soft white LED tape (1800 K - 3000 K) - 16.4 ft (5 m) reel		
LU-TO5-DL		Daylight LED tape (2500 K - 5000 K) - 16.4 ft (5 m) reel		
LU-CK1-TW		Wire/tape connectors (10 pack)		
LU-MK1		Mounting clips (20 pack)		
LU-WK1-TW		3 x 22 AWG (0.50 mm²) cable - 50 ft (15.2 m)		

NOTE: LED tape aluminum mounting channel and lens sold separately by others.

## **Specifications**

### **Regulatory Approvals**

- Power Supply
  - cULus Listed for USA and Canada
  - FCC Part 15 Class B compliant
  - ICES-003 compliant
  - US DoE Level VI compliant
  - Limited Power Supply
- Wireless Controller
  - cULus Listed for USA and Canada
  - FCC Part 15 Class B & C compliant
  - ICES-003 compliant
- Tunable white LED tape
  - cULus Listed for USA and Canada
    - · Indoor damp/dry location rated
    - · Wardrobe closet rated
  - FCC Part 15 Class B compliant
  - ICES-003 compliant

#### **Electrical**

Power Supply

Input: 120 V ~ 50/60 Hz, 1 A maxOutput: 24 V ─ 1500 mA, 36 W max

• Wireless Controller

— Input: 24 V===

- Output: 24 V== 0-1333 mA, 32 W max

#### Warranty

 The warranty will not cover issues caused by use of incompatible devices (including non-Lutron LED tapes and/or power supplies).

3691262a




# Lumaris Tunable White Tape Light


#### **Dimensions**

All dimensions shown as: in (mm)

#### Wireless Controller (HWL-TWC-WH) or RRL-TWC-WH)



#### **Power Cord**



3691262a




# Lumaris Tunable White Tape Light


### Dimensions (continued)

All dimensions shown as: in (mm)


#### Wireless Controller Mounting Bracket




#### Wireless Controller Mounting Screw




#### Wire to Tape Connector (LU-CK1-TW)




#### LED Tape (LU-T05-SW or LU-T05-DL)



#### Mounting Clip (LU-MK1)






Customer Assistance: 1.844.LUTRON1 (U.S.A./Canada) +44.(0)20.7680.4481 (Europe)



# Lumaris Tunable White Tape Light

## Wiring



• The length of the 24 V== cable coming from the power supply may be extended by cutting the plug ends off both the power supply and the wireless controller and adding cable of the appropriate gauge, from the table below to account for the distance.

Maximum Wire Length From the Power Supply to the Wireless Controller: ft (m)							
12 AWG	14 AWG	16 AWG	18 AWG	20 AWG			
(4.0 mm <sup>2</sup> )	(2.5 mm <sup>2</sup> )	(1.0 mm <sup>2</sup> )	(0.75 mm <sup>2</sup> )	(0.50 mm <sup>2</sup> )			
42.5 (13)	26.5 (8)	17 (5.2)	10.5 (3.2)	6.5 (2)			

- Maximum amount of cable allowed on the output of wireless controller is 10 ft (3.0 m). The cable can be added to the beginning or can be used to break up runs of tape light.
- 3 x 22 AWG (0.50 mm²) stranded cable is provided with the tape light kits or it can be ordered as Lutron P/N LU-WK1-TW
- For every wire-to-tape connector that is used on the output of a wireless controller, beyond 6, the maximum length of cable allowed is reduced by 6 in (152.4 mm).
- Maximum length of tunable white tape light is 16.4 ft (5m) total, regardless of whether tape is in a single run or broken up by cables.

The Lutron logo, Lutron, Clear Connect, HomeWorks, Lutron Connect, Lumaris, and Radio RA3 are trademarks or registered trademarks of Lutron Electronics Co., Inc. in the US and/or other countries.

All product names, logos, and brands are property of their respective owners.