

### SPECIFICATION SHEETS

# FM-MS70LED

Flush mount



NAME:	
TYPE:	
DATE:	
NOTES:	

### **SPECIFICATIONS**

WIRING:	Installs easily in traditional junction boxes.
HOUSING DETAILS:	This flush mount unit uses metal housing.
	The Apollo Series is available with or without the motion sensor. The motion sensor is a PIR sensor, with a detection range of 3' (1M) to 6' (2M) and a time delay of 5 minutes. Sensing no movement within that time period, the unit will shut off automatically.
OPTICS:	LED technology delivers 1000 lumens.
ELECTRICAL:	Easily connected to a 120V power supply via provided UL recognized driver.
	DAMP LOCATIONS and DIMMABLE. Motion sensor model is non-dimmable.
	Dimming down to 10% with most standard LED dimmers ( see list of approved products ).
	Certfied for use in closets. *
	Certifications: This product is ETL and Energy Star listed in USA & Canada.
	"*Meets NFPA70, NEC 410.16, C(1) requirements."
LENS:	White decorative acrylic frosted lens provides an even light distribution.

COLOR TEMPERATURE:	3K - 4K
OPERATING TEMPERATURE:	-20°C + 40°C
CRI:	90+
LUMEN OUTPUT:	1000 lumens
DIMMABLE:	Yes
WATTS:	13W
LED LIFE:	50,000 hours
WARRANTY:	5 years
VOLTAGE:	120V
DIAMETER:	7.13" (181mm)
HEIGHT:	1.3" (33.5mm)
INTEGRATED MOTION SENSOR:	Yes
MOTION SENSOR DETECTION RANGE:	3'-6' (1m-2m)

### APPLICATIONS





## FM-MS70LED

Flush mount

#### **DIMENSIONS**



### RATINGS









### ORDERING GUIDE

## **APOLLO FM-MS70 SERIES**

 Motion Sensor Series
 Color Temperature
 Finish

 FM-MS70-0510
 3K 3000K/90CRI/13W
 WH White

 4K 4000K/90CRI/13W
 WH White

Notes: Configure product using BOLD options: Ex: FM-MS70-0510-3K-WH