
Item no.: 222-413
Product description: COMPACT CONNECTOR; 3-CONDUCTOR TERMINAL BLOCKS; WITH LEVERS; MAX. CONTINUOUS SERVICE TEMPERATURE 85°C; CAGE CLAMP®CONNECTION



Packing unit 500 pieces

Product group	7 (Push Wire Conn.)
Cross section from [mm ²]	0,08 mm ²
Cross section to [mm ²]	2,5 mm ²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	14 AWG
Wiring method	e+f
Connection method	CAGE CLAMP®CONNECTION
Number of strands	3
Cross section from [mm ²]	0,08 mm ²
Cross section to [mm ²]	4 mm ²
Cross section from [AWG]	28 AWG
Cross section to [AWG]	12 AWG
Wiring method	f
Number of strands	3
Measured voltage EN	400 V
Measured shock voltage	4 kV
Pollution degree	2
Current intensity EN	32 A
Weight	4,153 g
Color	grey
Wiring type	Side-entry
No. of connection Points	3



Height	14,5 mm
Height	0,571 in
Width	17 mm
Width	0,669 in
Depth	20,5 mm
Depth	0,807 in
Strip length from	9 mm
Strip length to	10 mm
Strip length	0,37 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
222-413	BBJ	B/12/1298/03	450	32	0,5-4
222-413	ENEC15	DK140137-01	450	32	0,5-4
222-413	UL	E69654	600	20	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected