

Alter series

This aluminum retrofit LED panel offers the easiest and most practical solution for upgrading your outdated recessed lighting. For style and convenience, the removable outer trim attaches with magnetic fasteners, creating a seamless look. It can be easily retrofitted into existing 4" canisters or standard octagonal junction boxes.



*Model RTJB4-CC only

Model	Size	Watts	Delivered lumens	CRI	Color °T	Voltage
RTJB4-3K	4"	9 W	550 lm	90	3000 K	120 V
RTJB4-CC	4"	9 W	565 lm	90	2700, 3000, 3500, 4000, 5000 K	120 V

Specifications

Fits on octagonal junction boxes
 Fire rated alternative when mounted onto a fire rated junction box
 Minimal heat emission
 Aluminum construction
 Switch-selectable CCT: 2700 K/ 3000 K/3500 K/4000 K/5000 K (model RTJB4-CC only)
 Over 50,000 hours of service life
 Magnetic trim finish
 Air-tight certified as per ASTM E283-04
 Suitable for wet locations
 Refer to website for dimmer compatibility
 Ideal operating temperature: -20° to 40° C
 5-year warranty

Finish

- **BK** Black
- **WH** White





Accessories

- RTJB4-ACC**
4" recessed can mounting kit for RTJB4-XX - clips and E26 socket
- RTJB4-TRIM-BK**
4" recessed panel trim in black

Note

Other color °T and finishes available, but may require MOQ's and longer lead times. Please contact your DALs representative for more information.

RTJB4-XX



RTJB4-XX + RTJB4-ACC

