



Wire connector TA2.1 4 AWG...300 kcmil large with control wire voltage tap-off 3 units accessories for: 3VA4/5 125

Model	
product brand name	SENTRON
product designation	accessories
design of the product	circular conductor terminal
accessories	Wire connector
General technical data	
designation / of the terminal	TA2.1
type of electrical connection / with control wire tap	Yes
Connections according IEC	
connectable conductor cross-section	
<ul style="list-style-type: none"> for copper cable / stranded / minimum for copper cable / stranded / maximum for aluminum cable / stranded / minimum for aluminum cable / stranded / maximum 	25 mm ² 150 mm ² 25 mm ² 150 mm ²
stripped length	30,5 mm
tightening torque / when using copper cables	
<ul style="list-style-type: none"> stranded finely stranded 	25 - 150 mm ² : 28.5 Nm 25 - 150 mm ² : 28.5 Nm
Connections according UL	
permissible temperature / of connectable conductor / according to UL 486A-486B	75 °C
stripped length	1.2 in
connectable conductor cross-section	
<ul style="list-style-type: none"> for copper cable / stranded / minimum for copper cable / stranded / maximum for copper cable / finely stranded / minimum for copper cable / finely stranded / maximum for aluminum cable / stranded / minimum for aluminum cable / stranded / maximum 	4 AWG 300 kcmil 4 AWG 300 kcmil 4 AWG 300 kcmil
tightening torque / when using copper cables	
<ul style="list-style-type: none"> stranded finely stranded 	4 AWG - 350 kcmil: 252 lb-in 4 AWG - 350 kcmil: 252 lb-in
Further information	

Siemens has decided to exit the Russian market (see here).

<https://press.siemens.com/global/en/pressrelease/siemens-wind-down-russian-business>

Siemens is working on the renewal of the current EAC certificates.

Please contact your local Siemens office on the status of validity of the EAC certification if you intend to import or offer to supply these products to an EAC relevant market (other than the sanctioned EAEU member states Russia or Belarus).

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9133-0JC12>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9133-0JC12>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)






http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9133-0JC12

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

8/17/2022 

