



Siemens Low Voltage Circuit Protection Heavy Duty Safety Switches. 30A 3P 600V FUSED RECEPT SW TP12 W/WINDO

General technical data	
mechanical service life (operating cycles) typical	10000
fastening method	SURFACE
number of poles	3
suitability for operation	PROTECTION OF HEAVY DUTY PORTABLE EQUIPMENT
Electricity	
ampacity	30 A
supply voltage frequency rated value 50/60 Hz	Yes
Environmental conditions	
ambient temperature during operation maximum	85 °C
ambient temperature during operation minimum	-29 °C
Model	
product brand name	SIEMENS
product sub brand name	VBII
product type designation	HEAVY DUTY SWITCH
special product feature	ACCEPTS CROUSE-HINDS Arktype PLUGS VIEWING WINDOW
type of electrical connection	INTERLOCKED PLUG
Mechanical Design	
design of the housing	TYPE 12
design of the actuating element	SINGLE THROW
material	STEEL
General product approval	
certificate of suitability	UL98

last modified:

9/15/2021 

