



Siemens Low Voltage Molded Case Circuit Breakers Panelboard Mounting 240V Circuit Breakers - Type BL, 1-Pole, 120VAC are Circuit Protection Molded Case Circuit Breakers. Type: BL Application: Electrical Distribution Standard: UL 489 Voltage Rating: 120V Amperage Rating: 50A Trip Range: Thermal Magnetic Interrupt Rating: 10 AIC Number Of Poles: 1P

General technical data	
number of poles	1
suitability for operation	Electrical Distribution
Electricity	
continuous current rated value	50 A
Model	
product brand name	SIEMENS
type of electrical connection	BOLT-ON
Mechanical Design	
depth [in]	4 in
design of the product	BL
height [in]	1 in
width [in]	3 in
General product approval	
standard	UL 489

last modified:

1/6/2021 

