SIEMENS

Data sheet US2:HNFC361SW



Siemens Low Voltage Circuit Protection Heavy Duty Safety Switches. CSA 30A 3P 600V 3W NON-FUSED HD TYPE 4X $\,$

General technical data	
mechanical service life (operating cycles) typical	10000
fastening method	SURFACE
number of poles	3
suitability for operation	DISCONNECTING MEAN FOR SERVICE ENTRANCE / LOADS
Electricity	
ampacity	30 A
supply voltage frequency rated value 50/60 Hz	Yes
Model	
product brand name	SIEMENS
product type designation	HEAVY DUTY SWITCH
special product feature	VIEWING WINDOW
type of electrical connection	MECHANICAL LUGS
Mechanical Design	
design of the housing	TYPE 4X
design of the actuating element	SINGLE THROW
material	304 STAINLESS STEEL
General product approval	
certificate of suitability	UL98 / CSA

last modified: 9/16/2021 🖸