


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PER-FORMANCE, AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.









ACTUAL SIZE

ADHESIVE BACKING: PRESSURE SENSITIVE FOAM TAPE 0.040(1.0) THICK WITH PROTECTIVE LINER. MOUNT IS DESIGNED TO

SUPPORT 0.1316s.(59 g) MAX. WEIGHT ON A CLEAN, DRY, SMOOTH, GREASE-

PANDUIT	WEIGHT				
PART	bs/100 pcs				
NUMBER*	g /100 pcs				
ABM1M-AT	0.05 (23)				

TO APPLY MOUNTS:

- 1) REMOVE MOUNT FROM PROTECTIVE LINER.
- 2) PLACE IN DESIRED LOCATION.
- 3) APPLY PRESSURE TO TOP SURFACE OF MOUNT.

NOTES:

- *1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR MATERIAL, COLOR, AND PACKAGE SIZE.
- 2. USE MOUNTS WITH ONLY MINIATURE CABLE TIE CROSS SECTIONS.
- 3. MOUNT HAS A CONTINOUS OPERATING TEMPERATURE OF 180°F(82°C).
- 4. MOUNTS ARE SUPPLIED IN STRIPS OF FOUR.

DIMENSIONS IN BRACKETS ARE METRIC [mm]

I FREE SURFACE.					DIMENSIONS IN DIVISITE WE WILL WE WILL I					
							G00239DD_PB_ABM1M_AT_04			
										CORP. TINLEY PARK, ILLINOIS
										ABM1M-AT
4	3/23/05	TMSA		REVISED DIMENSION .123 FROM .120 UPDATED LEADER LINE FOR DIMENSION 0.055	GB023900	4				ADHESIVE BACKED MOUNT
3	3/29/04	JAD		CORRECT 3D GEOMETRY, UPDATE NOTE 1	GB023900	3				UNLESS OTHERWISE SPECIFIED, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: ALL DIMENSIONS ARE SIVEN
2	10-26-00	CGSM		CHANGED .158 DIMENSION TO REF	G8023900	2				(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25) (.XX) ±0.02 (0.51 ANGLES ± 5° IN THOSES, THIRD ANGLE PROJECTION.
1	12/20/96	۸۷		CHANGED NOTE 3	G802390D	1				DOWN BY CJG MAT'LS SCALE NONE
R	5/15/98	CJG		INITIAL RELEASE	G802390D	R				DATE 5/15/98 NYLON 6/6 DRAWING NO.
REV	DATE	BY	СНК	DESCRIPTION	ECN -	R	CUST	SUP		GB0239DD A