

# Eaton SUL06P-BK-KB-L

Catalog Number: SUL06P-BK-KB-L

Eaton slide dimmer, 300W LED-600W Halogen, #14 -12 AWG, Residential/ Light Commercial, Flush, 120V, Black, 68 Hz, Mark 10 Fluorescent, Single-pole, Three-way, 1,2,3+, Single-phase, Back and side wire, Polycarbonate, 300W - 600W 319250



## General specifications

Product Name	Catalog Number
Eaton slide dimmer	SUL06P-BK-KB-L
UPC	Product Length/Depth
032664759598	2.03 in
Product Height	Product Width
6.125 in	4.05 in
Product Weight	Certifications
0.01 lb	Contact Manufacturer

## Product specifications

### Phase

Single-phase

### Termination style

Back and side wire

### Load type

Mark 10 FLR

### Operating temperature - min

-4 °F

### Closure type

Maintained

### Wiring method

Back and side

### Mounting method

Flush

### Power consumption

300 - 600 W

### Style type

Slide

### Operating temperature - max

158 °F

### Frequency rating

60 Hz

### Voltage

120V

### Connection type

Side

Back

### Voltage rating

120 V

### Special features

No neutral required

### Switch type

Dimmer switch

### Color

Black

## Resources

### Brochures

[Universal slide dimmer instruction sheet](#)

[Universal dimmers sell sheet](#)

[Universal dimmers brochure](#)

[Universal slide dimmer brochure](#)

[Universal slide dimmer sell sheet](#)

### Installation instructions

[Universal slide dimmer](#)

### Installation videos

[How to install Eaton's universal slide dimmers](#)

### Multimedia

[Eaton SUL dimmers - how to change the color of the faceplate](#)

### Specifications and datasheets

[Eaton Specification Sheet - SUL06P-BK-KB-L](#)

[Universal slide dimmer spec sheet](#)

### User guides

[Universal dimmers quick reference guide](#)

Grade

Residential

Material

Polycarbonate

Number Of Poles

Single-pole, Three-way

Number of gangs

2

3

1

Surface finishing color

Black

Environmental conditions

Dry

Number of ways

Three-way

Application

Low-voltage/low-magnetic

Torque rating

14 lbf-inch



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)