

Eaton SUL06P-GY

Catalog Number: SUL06P-GY

Eaton slide dimmer, 300W LED-600W Halogen, #14 -12 AWG, Residential/ Light Commercial, Flush, 120V, Grey, 63 Hz, Mark 10 Fluorescent, Single-pole, Three-way, 1,2,3+, Single-phase, Back and side wire, Polycarbonate, 300W - 600W 319199



General specifications

Product Name	Catalog Number
Eaton slide dimmer	SUL06P-GY
UPC	Product Length/Depth
032664759543	2 in
Product Height	Product Width
4.25 in	2 in
Product Weight	Certifications
0.001 lb	Contact Manufacturer

Product specifications

Phase

Single-phase

Termination style

Back and side wire

Load type

Mark 10 FLR

Operating temperature - min

-4 °F

Closure type

Maintained

Wiring method

Back and side

Mounting method

Flush

Power consumption

300 - 600 W

Style type

Slide

Operating temperature - max

158 °F

Frequency rating

60 Hz

Voltage

120V

Connection type

Back

Side

Voltage rating

120 V

Special features

No neutral required

Switch type

Dimmer switch

Color

Gray

Resources

Brochures

[Universal slide dimmer instruction sheet](#)

[Universal slide dimmer brochure](#)

[Universal slide dimmer sell sheet](#)

[Universal dimmers sell sheet](#)

[Universal dimmers brochure](#)

Installation instructions

[Universal slide dimmer](#)

Installation videos

[How to install Eaton's universal slide dimmers](#)

Multimedia

[Eaton SUL dimmers - how to change the color of the faceplate](#)

Specifications and datasheets

[Eaton Specification Sheet - SUL06P-GY](#)

[Universal slide dimmer spec sheet](#)

User guides

[Universal dimmers quick reference guide](#)

Grade

Residential

Material

Polycarbonate

Number Of Poles

Single-pole, Three-way

Number of gangs

2

3

1

Surface finishing color

Gray

Environmental conditions

Dry

Number of ways

Three-way

Application

Low-voltage/low-magnetic

Torque rating

14 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia