

Eaton TRGF15B

Catalog Number: TRGF15B

Eaton tamper-resistant, self-test GFCI, 15A, 125V, Brown, Slim design

General specifications

Product Name	Catalog Number
Eaton slim GFCI receptacle	TRGF15B
UPC	Product Length/Depth
032664012990	1.03 in
Product Height	Product Width
4.19 in	1.69 in
Product Weight	Warranty
3.9 lb	Refer to warranty document.
Certifications	
cULus Listed	
NOM	



Product specifications

Circuit interrupter type

GFCI

Special features

Slim design

Type

Self-test

NEMA configuration

5-15R

Color

Brown

Wiring method

Back and side wire

Features

Tamper resistant

Voltage rating

125V

Allowable wire size

#14-10 AWG

Amperage Rating

15A

Torque rating

16 lbf-in

Packaging type

ED Box

Resources

Specifications and datasheets

[Tamper resistant slim GFCI receptacles spec sheet](#)

[Controlled slim GFCI spec sheet](#)

[GFCI Cross Reference](#)

[Tamper and weather resistant slim GFCI receptacles spec sheet](#)

[Standard slim GFCI spec sheet](#)

[Arrow Hart tamper resistant slim GFCI spec sheet](#)