

Eaton GF15BK

Catalog Number: GF15BK

Eaton self-test GFCI, 15A, 125V, Black, Slim design

General specifications

Product Name	Catalog Number
Eaton slim GFCI receptacle	GF15BK
UPC	Product Length/Depth
032664545313	1.03 in
Product Height	Product Width
4.19 in	1.69 in
Product Weight	Warranty
3.8 lb	Refer to warranty document.
Certifications	
cULus Listed	
NOM	



Product specifications

Circuit interrupter type

GFCI

Special features

Slim design

Type

Self-test

NEMA configuration

5-15R

Color

Black

Wiring method

Back and side wire

Voltage rating

125V

Allowable wire size

#14-10 AWG

Amperage Rating

15A

Torque rating

16 lbf-in

Packaging type

ED Box

Resources

Specifications and datasheets

[GFCI Cross Reference](#)

[Tamper resistant slim GFCI receptacles spec sheet](#)

[Tamper and weather resistant slim GFCI receptacles spec sheet](#)

[Standard slim GFCI spec sheet](#)

[Controlled slim GFCI spec sheet](#)

[Arrow Hart slim GFCI spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)