

# Eaton TRSGF20W

Catalog Number: TRSGF20W

Eaton GFCI receptacle, Tamper resistant, Self-test, #14 - 10 AWG, 20A, Residential, Commercial, Flush, 125 V, GFCI, Back and side wire, White, Brass, Receptacle, Tamper resistant, Polycarbonate, 5-20R, Two-pole, three-wire, grounding



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton GFCI receptacle	TRSGF20W
<b>UPC</b>	<b>Product Length/Depth</b>
032664739989	2.813 in
<b>Product Height</b>	<b>Product Width</b>
4.625 in	2 in
<b>Product Weight</b>	<b>Warranty</b>
0.398 lb	Refer to warranty document.
<b>Certifications</b>	
cULus Listed NOM	

## Product specifications

### Circuit interrupter type

GFCI

### Device type

Receptacle

### Color

White

### Face/body material

PVC

Polycarbonate

### Wiring method

Back and side wire

### Features

Tamper resistant

### Mounting method

Flush

### Allowable wire size

#14 - 10 AWG

### Amperage Rating

20A

### Contact material

Brass

### Type

Self-test

### NEMA configuration

5-20R

### Environmental conditions

Tamper resistant

### Receptacle type

Two-pole, three-wire, grounding

### Voltage rating

125V

### Application

Residential

Commercial

### Torque rating

## Resources

### Installation instructions

[Installing and testing a GFCI receptacle instruction sheet](#)

### Multimedia

[What is a Ground Fault Circuit Interrupting \(GFCI\) receptacle?](#)

### Specifications and datasheets

[Eaton Specification Sheet - TRSGF20W](#)

[Arrow Hart specification grade GFCI receptacles spec sheet](#)

16 lbf-inch

---



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)