

Eaton TWRGF20V

Catalog Number: TWRGF20V

Eaton tamper and weather-resistant, self-test GFCI, 20A, 125V, Ivory, Slim design



General specifications

Product Name	Catalog Number
Eaton slim GFCI receptacle	TWRGF20V
UPC	Product Length/Depth
032664013409	1.03 in
Product Height	Product Width
4.19 in	1.69 in
Product Weight	Warranty
3.9 lb	Refer to warranty document.
Certifications	
cULus Listed	
NOM	

Product specifications

Circuit interrupter type

GFCI

Special features

Slim design

Type

Self-test

NEMA configuration

5-20R

Color

Ivory

Wiring method

Back and side wire

Features

Tamper resistant

Weather resistant

FedSpec Certified

Voltage rating

125V

Allowable wire size

#14-10 AWG

Amperage Rating

20A

Torque rating

16 lbf-in

Packaging type

ED Box

Resources

Specifications and datasheets

[Tamper resistant slim GFCI receptacles spec sheet](#)

[Controlled slim GFCI spec sheet](#)

[GFCI Cross Reference](#)

[Tamper and weather resistant slim GFCI receptacles spec sheet](#)

[Standard slim GFCI spec sheet](#)

[Arrow Hart tamper and weather resistant slim GFCI spec sheet](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)