

Eaton TRGF20RD

Catalog Number: TRGF20RD

Eaton tamper-resistant, self-test GFCI, 20A, 125V, Red, Slim design



General specifications

Product Name	Catalog Number
Eaton slim GFCI receptacle	TRGF20RD
UPC	Product Length/Depth
032664013119	1.03 in
Product Height	Product Width
4.19 in	1.69 in
Product Weight	Warranty
3.9 lb	Refer to warranty document.
Certifications	
cULus Listed NOM	

Product specifications

Circuit interrupter type

GFCI

Special features

Slim design

Type

Self-test

NEMA configuration

5-20R

Color

Red

Wiring method

Back and side wire

Features

Tamper resistant

FedSpec Certified

Voltage rating

125V

Allowable wire size

#14-10 AWG

Amperage Rating

20A

Torque rating

16 lbf-in

Packaging type

ED Box

Resources

Specifications and datasheets

[Tamper resistant slim GFCI receptacles spec sheet](#)

[Tamper and weather resistant slim GFCI receptacles spec sheet](#)

[Controlled slim GFCI spec sheet](#)

[GFCI Cross Reference](#)

[Standard slim GFCI spec sheet](#)

[Arrow Hart tamper resistant slim GFCI spec sheet](#)