

# Eaton TRGF20GY

Catalog Number: TRGF20GY

Eaton tamper-resistant, self-test GFCI, 20A, 125V, Gray, Slim design



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton slim GFCI receptacle	TRGF20GY
<b>UPC</b>	<b>Product Length/Depth</b>
032664013096	1.03 in
<b>Product Height</b>	<b>Product Width</b>
4.19 in	1.69 in
<b>Product Weight</b>	<b>Warranty</b>
3.9 lb	Refer to warranty document.
<b>Certifications</b>	
cULus Listed	
NOM	

## Product specifications

### Circuit interrupter type

GFCI

### Special features

Slim design

### Type

Self-test

### NEMA configuration

5-20R

### Color

Gray

### Wiring method

Back and side wire

### Features

Tamper resistant

FedSpec Certified

### Voltage rating

125V

### Allowable wire size

#14-10 AWG

### Amperage Rating

20A

### Torque rating

16 lbf-in

### Packaging type

ED Box

## Resources

### Specifications and datasheets

[Tamper resistant slim GFCI receptacles spec sheet](#)

[Controlled slim GFCI spec sheet](#)

[GFCI Cross Reference](#)

[Tamper and weather resistant slim GFCI receptacles spec sheet](#)

[Standard slim GFCI spec sheet](#)

[Arrow Hart tamper resistant slim GFCI spec sheet](#)