

# Eaton GF20V

Catalog Number: GF20V

GFCI-20AMP-LITED (CTO DUP PFAT 5-20R) - GF20V.



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton slim GFCI receptacle	GF20V
<b>UPC</b>	<b>Product Length/Depth</b>
032664012341	1.03 in
<b>Product Height</b>	<b>Product Width</b>
4.19 in	1.69 in
<b>Product Weight</b>	<b>Warranty</b>
3.8 lb	Refer to warranty document.
<b>Certifications</b>	
cULus Listed	
NOM	

## Product specifications

### Circuit interrupter type

GFCI

### Special features

Slim design

### Type

Self-test

### NEMA configuration

5-20R

### Color

Ivory

### Wiring method

Back and side wire

### Features

FedSpec Certified

### Voltage rating

125V

### Allowable wire size

#14-10 AWG

### Amperage Rating

20A

### Torque rating

16 lbf-in

### Packaging type

ED Box

## Resources

### Specifications and datasheets

[Controlled slim GFCI spec sheet](#)

[Tamper resistant slim GFCI receptacles spec sheet](#)

[Standard slim GFCI spec sheet](#)

[GFCI Cross Reference](#)

[Tamper and weather resistant slim GFCI receptacles spec sheet](#)

[Arrow Hart slim GFCI spec sheet](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)