

Eaton TRSGF15W

Catalog Number: TRSGF15W

Eaton ground fault circuit interrupter receptacle, 15A, 125V, Back wire and side wire, GFCI, White, Brass, Receptacle, Tamper resistant, PVC, 5-15R, Two-pole, three-wire, grounding



General specifications

Product Name	Catalog Number
Eaton GFCI receptacle	TRSGF15W
UPC	Product Length/Depth
032664739903	2.813 in
Product Height	Product Width
4.625 in	2 in
Product Weight	Certifications
0.41 lb	NOM cULus Listed

Product specifications

Circuit interrupter type

GFCI

Device type

Receptacle

Color

White

Face/body material

PVC

Polycarbonate

Wiring method

Back and side wire

Features

Tamper resistant

Mounting method

Flush

Allowable wire size

#14 - 10 AWG

Amperage Rating

15A

Number Of Poles

Two-pole

Contact material

Brass

Type

Self-test

NEMA configuration

5-15R

Environmental conditions

Tamper resistant

Number of wires

Three-wire

Receptacle type

Two-pole, three-wire, grounding

Voltage rating

125V

Resources

Installation instructions

[Installing and testing a GFCI receptacle instruction sheet](#)

Multimedia

[What is a Ground Fault Circuit Interrupting \(GFCI\) receptacle?](#)

Specifications and datasheets

[Eaton Specification Sheet - TRSGF15W](#)

[Arrow Hart specification grade GFCI receptacles spec sheet](#)

Application

Residential

Commercial

Torque rating

16 lbf-inch



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)