

Eaton AH1254W-BOX

Catalog Number: AH1254W-BOX

Eaton power receptacle AH1254-BK-BX-L



General specifications

Product Name	Catalog Number
Eaton Arrow Hart power device receptacle	AH1254W-BOX
	UPC
	032664005763
Product Length/Depth	Product Height
2.17 in	3.69 in
Product Width	Product Weight
2.25 in	0.39 lb

Warranty

Refer to warranty document.

Product specifications

Special features

Canadian mounting strap

Color

White

Wiring method

Back

Features

Canadian mounting strap

Mounting method

Flush

Amperage Rating

30A

Number Of Poles

Two-pole

Base color

White

Type

Flush mount receptacle

NEMA configuration

6-50R

Design type

Receptacle

Connection type

Screw

Style

Power

Number of wires

3

Receptacle type

Two-pole, three-wire, grounding

Voltage rating

250V

Resources

Brochures

Flush mount receptacles sell sheet

Specifications and datasheets

FMR NEMA 6-30, 6-50 spec sheet



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)