

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L5 and L5R.

CONSTRUCTION

All finishes are one-piece aluminum open reflectors with integral white flange.

INSTALLATION

Socket to trim interface.

Retaining clips pull and snap onto top of reflector to hold trim inside housing.

LISTINGS

U.L. Listed to U.S. and Canadian safety standards.


Damp location listed.

WARRANTY

1-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms_and_conditions.aspx

Actual performance may differ as a result of end-user environment and application.

Note: Specifications subject to change without notice.



5" Finishing Trim



OPEN DEEP


Narrow Flange



Height: 5-3/4 (14.6) Lamp opening: 5-1/8 (13)

Diameter: 6-3/8 (16.2)

All dimensions are inches (centimeters) unless otherwise indicated.



ORDERING INFORMATION Lead times will vary depending on options selected. Consult with your sales representative.					
502	502				
Series	Finish				
502	Anodized finish ¹				
	A Clear diffuse				
	AZ Clear specular				
	BLZ Black specular				

Housing Compatibility: Housing and trim ordered separately.				
Application	Source	Maximum wattage	Housing	
		60 PAR38	L5, L5R	
	Incandescent	65 BR30		
IC		50 R20		
		75 PAR30 short neck		

502

Accessories: Order as separate catalog number.				
CR	T5	5" goof ring, white		

DOWNLIGHTING

finish, see <u>502-TOR</u> spec sheet.

¹ Not available with torsion springs or white finish. For white

502 5" Open Deep Full Reflector Trim

 $For BR \ and \ PAR \ reflector \ lamps, see \ lamp \ manufacturer's \ published \ raw \ lamp \ data \ for \ photometrics.$