JUNO

Project:	
Fixture Type:	
Location:	
Contact/Phone:	

TRAC-MASTER® Mounting Accessories MONOPOINTS and SPECIAL MOUNTINGS

D1.2.0

Example: T40N BL

PRODUCT DESCRIPTION

Special adapters permit the flexibility of mounting trac lights in various ways to meet special requirements.

Line Voltage Monopoint Adapters

T40N	T40F	T41N	T42N
BL, SL, WH	BL, WH	BL, WH	BL, WH
Monopoint Adapter	Flush Monopoint Adapter	Duo-Point Adapter	Weighted Base
Mounts directly to outlet box. Accepts one 120V Juno trac fixture.	Mounts directly to 4" outlet box only. Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter.	Mounts directly to an outlet box. Accepts two 120V Juno trac fixtures.	For portable use. Supplied with 8' cord and plug. Accepts one 120V Juno trac fixture.
5/8"I	<u>5 1/4"</u> 1/32" =	4" 4" 5/8"	4 3/4" 5/8"I 00000000

Line Voltage Coil - Cord Clamp-Ons

Example: T132 WH

T132	T133
BL, WH	BL, WH
120V Monopoint with Trac Adapter	120V Monopoint with Male Plug
120V Monopoint with trac adapter for electrical connection to Trac. Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter.	120V Monopoint with male plug (120V) attaches to receptacle. Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter.
2' Coil Cord extends to 5'. 1-3/4" Clamp opening. 1 5/8" 3 1/8"	

TRAC-MASTER® Mounting Accessories **MONOPOINTS** and SPECIAL MOUNTINGS


D1.2.0

Line Voltage Extension Wands	Examples: TEW 12IN BL
TEW	TEWS
12IN, 18IN, 24IN, 36IN, 48IN	
BL, SL, WH	BL, WH
Line Voltage Extension Wands	24" Wand Slope Adapter
For use with one or two circuit trac and line voltage monopoints. Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter. Note: SL finish for TEW only available in 18" and 24" lengths and in limited quantities	Accepts one 120V Juno trac fixture with <u>standard size</u> trac adapter.
C	

Line Voltage Slope Ceiling Adapter Examples: T95 BL

T95		
BL, WH		
Slope Ceiling Adapter		
Attaches to trac, permitting Trac-Master or Trac-Lites Trac fixtures with <u>standard size</u> trac adapter to be hung vertically from sloped ceiling, 90° maximum adjustable		
4 3/4" max.		

T252L, R Series Low Voltage Monopoint Adapters Example: T58 BL



TRAC-MASTER® Mounting Accessories MONOPOINTS and SPECIAL MOUNTINGS

D1.2.0

Low Voltage Extension Wands Examples: TWL 12IN BL, TWLED 18IN W		
TWL12	TWLED	
12IN, 18IN, 24IN, 36IN, 48IN	12IN, 18IN, 24IN, 36IN, 48IN	
BL, SL, WH	BL, SL, WH	
Low Voltage Extension Wands	T252L Extension Wands	
Accepts one Juno 12V low voltage spotlight. Attaches to T537 Power Pack.	Attaches between T252L fixture housing and LED driver housing to move the light source closer to illumination point without lowering the trac mounting height.	

Steel Safety Cable (Lanyard) Example: TSSC 18IN

