JUNO

Contact/Phone:

TRAC-MASTER®

Recessed Trac System

TRAC SECTIONS, **CONNECTORS & ACCESSORIES**

TREC

Project: Fixture Type: Location:

PRODUCT DESCRIPTION

Flanged, single-circuit trac sections for recessing into plaster board or suspended grid ceiling. For straight runs only. Accepts all Trac-Master and Trac-Lites trac fixtures.

PRODUCT SPECIFICATIONS

Construction Extruded aluminum flanged channel • One-piece thermoplastic insulator • Injection molded polycarbonate dead-end with set screw • Standard lengths may be cut-to-length by installer.

Electrical Two 12 gauge solid copper conductors • Rated 20 amps at 120 volts • Aluminum channel used as system ground

• One-piece insulator insures consistent conductor spacing for reliable electrical contact • Insulating bushings supplied at mounting hole locations to prevent shorts to ground.

Labels UL listed, CSA certified.

PRODUCT INSTALLATION

Debossed polarity line provides visual cue to proper trac, trac connector and fixture alignment • Supplied with toggle bolts


 Insulator stays same length as extrusion to simplify field-cutting of trac Connectors and feeds simply push into trac sections.

WARRANTY - 1-year limited warranty. This is the only warranty provided and no other statements in this specification sheet create any warranty of any kind. All other express and implied warranties are disclaimed. Complete warranty terms located at: www.acuitybrands.com/support/warranty/termsand-conditions

Note: Actual performance may differ as a result of end-user environment and application.

Specifications subject to change without notice.

DIMENSIONS



Example: TREC 8FT WH

ORDERING INFORMATION Example: TREC 8FT W			
Series	Length	Finish	
TREC Trac-Master Recessed Track Section	4FT 4-foot track section; actual length 43-7/8" 8FT 8-foot track section; actual length 91-7/8"	WH White	

Trac Connectors

T121	T123	
WH	WH	
End Feed Connector	Mini Straight Connector	
With wiring box for electrifying trac. Requires above-ceiling access.	Mechanically and electrically joins two trac sections end to end.	
2 5/8" 3 7/8"	3/8" 	

Accessories

T31N	T32	Т33
BL, SL, WH	BL, WH	BL, WH
Pendant Adapter	Plant or Utility Hook	Outlet Adapter
Adapts corded, swag or chain-hung fixture to trac. Includes loop hook for chain installation and strain relief for direct cord suspension. Chain installation accepts cord diameters up to 0.270" and supports up to 15 lbs. Strain relief installation accepts cord diameters of 0.170" to 0.255", type SVT 18/3, and supports up to 5 lbs. May also be specified with GTYPE, HTYPE or LTYPE Alternate Mounting Adapters (i.e. T31 N HTYPE WH). 5A max. UL Listed. Not available in HTYPE BL.	Supports up to 25 lbs. Not UL Listed.	Provides electrical recepta- cle. Not UL Listed.
3-5/8" 3-5/8" 2" 2"	11/4"	2"

Note: GTYPE, HTYPE and LTYPE available in BL or WH finishes only.