



Wiremold
Desktop Power Center Slim, 2 Outlets, USB A/C, Black, 6ft Cord
Part No. WSPC220CBK



Desktop Power Center with two (2) or three (3) 15A tamper resistant power receptacles and two (2) smart USB ports, one (1) USB-A and one (1) USB-C, that provide 3.1A. Includes a screw-in mounting plate for forward-facing outlets, under-table mount bracket, and clamp mounting kit. Available with either a 6' (1.83m) or 10' (3.05m) power cord.

Features & Benefits

Multiple options

Two versions with reliable power and charging – one with three (3) tamper-resistant power outlets and two (2) USB charging ports (3.1A) and one with two (2) tamper-resistant power outlets and two (2) USB charging ports (3.1A).

Easy connection to power sources

6' (1.83m) or 10' (3.05m) 14 gauge cord easily reaches walls and floors.

Less clutter, more functionality

A sleek slim design fits unobtrusively on work surfaces.

Table Thickness

Supports tables from 0.5" to 1.5" for the clamp mount. Under table bracket mount supports 1" to 1.5".

Intelligent and energy efficient

Smart charging capability that recognizes devices and when to shut off during peak loads.

Simple and flexible installation

Mounting kits include options for both horizontal and vertical applications.

Seamlessly blends into your space

Two color choices that work with any environment.

Included Mounting Kit

Includes several mounting options for use under and above table surfaces for any environment.

Specifications

General Info

Product Line	Wiremold	Color	Black
UPC Number	786776192551	Country Of Origin	China
Number of Receptacles	2	Application Sector	Commercial
Warranty Type	1-Year	Type	Desktop Power Center

Listing Agencies / 3rd Party Agencies

ETL Listed	Yes	ETL ListingNumber	103010043BOX-001
------------	-----	-------------------	------------------

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Is Tamper-Resistant	Yes	Cord Length	6 ft
---------------------	-----	-------------	------

Number of USBs	2	Indoor/Outdoor	Indoor
----------------	---	----------------	--------

Mounting Type	On Surface	Number of Outlets	2
---------------	------------	-------------------	---
