



Manual Cable Cutter, up to 1000 kcmil Copper and Aluminum

By Burndy
Catalog # [MCC1000](#)

Manual Cable Cutter, up to 1000 kcmil CU/AL.



Features

- High quality design and construction
- Rugged high quality steel blades
- Fiberglass handles with soft grips

Application

Cutting

General

Application - For Use On	Aluminum, Copper Cable
EU RoHS Indicator	Yes
Sub Brand	HYTOOL
Tool Type	Manual Cable Cutter
Type	Cutter
UPC	781810174869
UPC 12 Digit	7818101748699

Dimensions

Cable Insulation Diameter Maximum	1.900 in
Length	32 in
Weight	9 lb
Width	6 in

Conductor Related

Crimping Ranges	Cutting Capacity : Copper upto 1000 kcmil; Aluminum: upto 1000 kcmil
-----------------	--

Certifications and Compliance

Standards - RoHS Compliance EX Status

Logistics

Minimum Pack Quantity	1
Package Contents	Tool only

Product Assets

- [Catalogs - Cutters \(2150\)](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - SE211277-01_A](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-MCC1000-SPEC-EN | REV 10/2023