

# Ratchet Cable Cutter, Cuts up to 750 kcmil Copper and Aluminum, **Maximum Insulation Diameter 1.62"**

By Burndy Catalog # RCC750HD

Ratchet Cable Cutter, Cuts up to 750 kcmil CU/AL, Max. Ins. Dia. 1.62".



## **Features**

- · Patented high strength steel blades
- Quick release, bi-directional ratchet mechanism
- Rapid blade advance

## **Application**

UPC 12 Digit

Cutting

#### General

Application - For Use On Aluminum, Copper Cable **EU RoHS Indicator** Yes Sub Brand RATCHET CUTTER Tool Type Ratchet Cable Cutter Type Cutter UPC 781810350058

7818103500588

# **Dimensions**

Cable Insulation Diameter 1.620 in Maximum

Dimensions 10.35 in x 1.75 in x 4.69 in

4.69 in Height 10.35 in Length Weight 2.56 lb Width 1.75 in

# **Certifications and Compliance**

Standards - RoHS Compliance EX

Status

# Logistics

Minimum Pack Quantity

Package Contents Tool only

## **Product Assets**

Catalogs - Cutters (2150) Customer Notices - Prop 65 Notice Sales Drawings - 10032330-01

