



YAV14BOX, Uninsulated Ring Terminal, #20-14 AWG Str, #20-AWG Sol, 1-Hole, #8-10 Stud

By Burndy
Catalog # YAV14BOX



Copper Compression Lug, Ring Tongue w/ Inspection Hole, 1 Hole, 20-14 AWG/20-12 AWG, #8-#10 Stud, Short Barrel, Tin Plated, Wire strip length: 9/32".

Application

For Use On Copper Commercial (Code) Cable, Type AN Aircraft Cable And Extra Flexible Conductors, Industrials, Hospitals, Electric Utilities, Shipboard And Marine, Computers, Steel Mills, Mining Equipment And Other Equipment That Is Subject To Vibration Or Requiring Dependable Electrical Performance

General

Connector Type	Ring Terminal
EU RoHS Indicator	Yes
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Ring
Plated	Y
Plating Type	Tin
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Ring Tongue
UPC	781810542200

Dimensions

Dimension - B Length fraction	1/4 in
Dimension - B Length inch	0.25 in
Dimension - Bolt Size fraction	#8 - #10
Dimension - D inch	0.40 in
Dimension - L Length Overall mm	20 mm
Dimension - Length Overall inch	0.78 in
Dimension - N inch	0.16 in
Dimension - Outside Diameter inch	0.16 in
Dimension - Pad Width inch	0.30 in
Dimension - Strip Length inch	9/32 in
Dimension - Stud Size inch	#8;#10
Dimension - Z inch	0.24 in

Conductor Related

Conductor - Copper Solid Size	20 AWG ;18 AWG;17 AWG;16 AWG;15 AWG;14 AWG;13 AWG;12 AWG
Conductor - Copper Solid Size Range	20 AWG -12 AWG
Conductor - Copper Str Aircraft Size Range	AN 16-AN 14
Conductor - Copper Str Size	20 AWG;18 AWG;16 AWG;14 AWG
Conductor - Copper Str Size Range	20 AWG-14 AWG
Conductor Size	16 - 14 AWG
Conductor Type	<ul style="list-style-type: none"> • CU C Solid-Size • CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL486
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200
Minimum Pack Quantity	100
Pallet Quantity	96000

Product Assets

- [3D Models - YAV14BOX_MODEL-IGES](#)
- [3D Models - YAV14BOX_MODEL-PDF](#)
- [3D Models - YAV14BOX_MODEL-STEP](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - 50094160](#)
- [Technical Solutions - BURNDY_YAV14BOX_Specsheet](#)



A proud member of the Hubbell Family.

©2023 Hubbell Incorporated. All rights reserved.
BRDY-YAV14BOX-SPEC-EN | REV 10/2023