



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




NOTES:


1. PART NUMBERS:
  - A. SEE SHEET 2 FOR 12 FIBER UNIVERSAL PART NUMBERS.
  - B. SEE SHEET 3 FOR 24 FIBER UNIVERSAL PART NUMBERS.
2. CASSETTE WEIGHT:
  - A. 12 FIBER = 3.60oz [ 102g ]
  - B. 24 FIBER = 4.30oz [ 122g ]
3. DIMENSIONS IN BRACKETS ARE METRIC.




12 FIBER FRONT VIEW



24 FIBER FRONT VIEW



12 FIBER




24 FIBER

|   |          |   |       |
|---|----------|---|-------|
| TITLE   |          | OPTICOM 12 AND 24 FIBER LC CASSETTE (UNIVERSAL) |       |
|   |          | CUSTOMER DRAWING                                |       |
| ITEM REVISION NAME  |          | 10F113CP/00                                     |       |
| DATASET FILE NAME   |          | 10F113CP_DC/00C                                 |       |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ] |          | MATERIAL:                                       |       |
| .x ± .03 [ .8 ]   |          | .xxx ± .005 [ .127 ]                            |       |
| .xx ± .01 [ .25 ]   |          | ANGLES ± 5 °                                    |       |
| THIRD ANGLE PROJECTION  |          | DRAWING NUMBER:                                 |       |
| 10F113CP-DC   |          | 10F113CP-DC                                     |       |
| DRAWN BY  | DATE     | CHK   | SCALE |
| SAT   | 06-26-18 | PJI   | NONE  |
| SHT 1 OF 3  |          | SIZE  |       |
| A   |          | A   |       |

| OOC | 8/30/21  | JSP | JGD | JH  | B. ADDED OM5.              | 10F113CP-DC |
|-----|----------|-----|-----|-----|----------------------------|-------------|
| OOB | 05-29-19 | SAT | DWW | EJH | A. ADDED P/N FC29N-24-LAU. | 10F113CP-DC |
| OOA | 06-28-18 | SAT | PJI | EJH | RELEASED TO PRODUCTION     | 10F113CP-DC |
| REV | DATE     | BY  | CHK | APR | DESCRIPTION                | ECN         |

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| 12 FIBER DUPLEX LC CASSETTE - UNIVERSAL |   |
|---|---|
| PART NUMBER                             | DESCRIPTION                                       |
| FC2XN-12-10U                            | 12 FIBER 50/125um OM3, STANDARD LOSS              |
| FC2ZN-12-10U                            | 12 FIBER 50/125um OM4, STANDARD LOSS              |
| FC29N-12-10U                            | 12 FIBER 9/125um OS2, STANDARD LOSS               |
| FC2X0-12-10U                            | 12 FIBER 50/125um OM3, OPTIMIZED LOSS             |
| FC2Z0-12-10U                            | 12 FIBER 50/125um OM4, OPTIMIZED LOSS             |
| FC2XA-12-10U                            | 12 FIBER 50/125um OM3, ULTRA LOW LOSS             |
| FC2ZA-12-10U                            | 12 FIBER 50/125um OM4, ULTRA LOW LOSS             |
| FC2SA-12-10U                            | 12 FIBER 50/125um OM4+, SIG. CORE, ULTRA LOW LOSS |
| FC2WA-12-10U                            | 12 FIBER 50/125um OM5, ULTRA LOW LOSS             |
| FC2W0-12-10U                            | 12 FIBER 50/125um OM5, OPTIMIZED LOSS             |




12 FIBER UNIVERSAL - FIBER LAYOUT

|     |      |    |     |     |             |  |          |          |     |  |            |  |      |
|-----|------|----|-----|-----|-------------|--|----------|----------|-----|--|------------|--|------|
|     |      |    |     |     |             | TITLE  |          |          |     | OPTICOM 12 AND 24 FIBER LC CASSETTE<br>(UNIVERSAL) |            |  |      |
|     |      |    |     |     |             |  |          |          |     | CUSTOMER DRAWING                                   |            |  |      |
|     |      |    |     |     |             | ITEM REVISION NAME   |          |          |     | 10F113CP/00  |            |  |      |
|     |      |    |     |     |             | DATASET FILE NAME  |          |          |     | 10F113CP_DC/00C                                    |            |  |      |
|     |      |    |     |     |             | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [mm] |          |          |     | MATERIAL:  |            |  |      |
|     |      |    |     |     |             | .x ± .03 [ .8 ]      .xxx ± .005 [ .127 ]                          |          |          |     | SEE NOTES SHEET 1                                  |            |  |      |
|     |      |    |     |     |             | .xx ± .01 [ .25 ]      ANGLES ± 5 °                                |          |          |     | DRAWING NUMBER:                                    |            |  |      |
|     |      |    |     |     |             | SEE SHEET 1 FOR REVISION HISTORY                                   |          |          |     | 10F113CP-DC  |            |  |      |
| REV | DATE | BY | CHK | APR | DESCRIPTION | ECN  | DRAWN BY | DATE     | CHK | SCALE  | SHT 2 OF 3 |  | SIZE |
|     |      |    |     |     |             |  | SAT      | 06-26-18 | PJI | NONE   |            |  | A    |

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

24 FIBER DUPLEX LC CASSETTE - UNIVERSAL

| PART NUMBER  | DESCRIPTION                                       |
|--------------|---|
| FC2XN-24-10U | 24 FIBER 50/125um OM3, STANDARD LOSS              |
| FC2ZN-24-10U | 24 FIBER 50/125um OM4, STANDARD LOSS              |
| FC29N-24-10U | 24 FIBER 9/125um OS2, STANDARD LOSS               |
| FC2X0-24-10U | 24 FIBER 50/125um OM3, OPTIMIZED LOSS             |
| FC2Z0-24-10U | 24 FIBER 50/125um OM4, OPTIMIZED LOSS             |
| FC2XA-24-10U | 24 FIBER 50/125um OM3, ULTRA LOW LOSS             |
| FC2ZA-24-10U | 24 FIBER 50/125um OM4, ULTRA LOW LOSS             |
| FC2SA-24-10U | 24 FIBER 50/125um OM4+, SIG. CORE, ULTRA LOW LOSS |
| FC29N-24-LAU | 24 FIBER OS2 LC/APC, STANDARD LOSS                |
| FC2WA-24-10U | 24 FIBER 50/125um OM5, ULTRA LOW LOSS             |
| FC2W0-24-10U | 24 FIBER 50/125um OM5, OPTIMIZED LOSS             |



24 FIBER UNIVERSAL - FIBER LAYOUT

| REV | DATE | BY | CHK | APR | DESCRIPTION                      | ECN | TITLE  | MATERIAL:         | DRAWING NUMBER: | SIZE          |
|-----|------|----|-----|-----|----------------------------------|-----|--|-------------------|-----------------|---------------|
|     |      |    |     |     |                                  |     | OPTICOM 12 AND 24 FIBER LC CASSETTE (UNIVERSAL)  | SEE NOTES SHEET 1 | 10F113CP-DC     | A             |
|     |      |    |     |     | SEE SHEET 1 FOR REVISION HISTORY |     | CUSTOMER DRAWING   |                   |                 |               |
|     |      |    |     |     |                                  |     | ITEM REVISION NAME<br>10F113CP/00  |                   |                 |               |
|     |      |    |     |     |                                  |     | DATASET FILE NAME<br>10F113CP_DC/00C   |                   |                 |               |
|     |      |    |     |     |                                  |     | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [mm]<br>.x ± .03 [ .8 ]      .xxx ± .005 [ .127 ]<br>.xx ± .01 [ .25 ]      ANGLES ± 5 ° |                   |                 |               |
|     |      |    |     |     |                                  |     | THIRD ANGLE PROJECTION   |                   |                 |               |
|     |      |    |     |     |                                  |     | DRAWN BY<br>SAT  | DATE<br>06-26-18  | CHK<br>PJI      | SCALE<br>NONE |
|     |      |    |     |     |                                  |     |  |                   | SHT 3 OF 3      |               |