



Siemens Low Voltage Molded Case Circuit Breakers General Purpose MCCBs are Circuit Protection Molded Case Circuit Breakers. 1-Pole circuit breaker type BQH. Rated 120V (020A) (AIR 22 kA). Special features: Load side lugs are included.

General technical data	
number of poles	1
suitability for operation	Electrical Distribution
Electricity	
continuous current rated value	20 A
Model	
product brand name	SIEMENS
type of electrical connection	BOLT-ON
Mechanical Design	
depth [in]	3 in
design of the product	BQ
height [in]	4 in
width [in]	1 in
General product approval	
standard	UL 489

last modified:

1/6/2021 

